



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL A
(SCALE 2X)






PANDUIT P/N	WEIGHT
PZ1B2G3BN03L1	30 lb (13.6 kg)

NOTES:

- IDENTIFICATION: 2RU HORIZONTAL, (3) L6-30 NETWORKED 208V / 50A / THREE-PHASE DELTA POU

PART NO.	COLOR
PZ1B2G3BN03L1	BLACK
- ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
- DIMENSIONS IN PARENTHESES ARE METRIC (mm).
- CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/PHASE (X,Y,Z) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.
- UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.
- RoHS COMPLIANT.
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- MAXIMUM AVAILABLE INPUT POWER = 17.3 KW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01A	9-10-12	PIP		A. UPDATED DETAIL A. B. ADDED NOTE #9 C. UPDATED NOTE #5 & 8.	09V098US				
00A	6-27-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098US				

MODEL FILENAME	09V098US/01.PRT	
CAD FILENAME/LAYERS	09V098US_DC/01A.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS		
2RU HORIZONTAL (3) L6-30 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES: X.X +/- 0.03, X.XX +/- 0.015, X.XXX +/- 0.005 [METRIC - MILLIMETER] X +/- 0.8, X.X +/- 0.4, X.XX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
DRAWN BY MAV	MAT'L:	SCALE NONE
DATE 6-27-11		DWG B
CHK'D KRKE		DWG B
		DWG NO. 09V098US
		DWG B