


1. IDENTIFICATION: VERTICAL, MIXED (16) C-13 & (4) C-19 & (2) L6-30
NETWORKED 208V / 60A / 3-PHASE DELTA POU



<u>PART NO.</u>	<u>COLOR</u>
QZ1B2G5BN2271	BLACK

2. ACCESSORY COMPONENTS:
 (4) 10-32 x 1/2" MOUNTING SCREWS
 (4) 10-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/PHASE (X,Y,Z) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.




5. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.

6. RoHS COMPLIANT.


7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 17.3 KW


9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



PLUG
60 AMP, 250V x 3~ DELTA
3P/4W
IEC 60309, SPLASHPROOF



SIXTEEN (16)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



FOUR (4)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19



TWO (2)
RECEPTACLES
30 AMP, 250V
TWIST LOCK
NEMA L6-30R

01A	9-10-12	PIP	MRWA	A. UPDATED DETAIL A. B. CORRECTED PART NUMBER C. UPDATED WEIGHT D. UPDATED NOTE 5		09V098UT				
00A	6-27-11	MAV	KRKE	RELEASED TO PRODUCTION		09V098UT				
REV	DATE	BY	CHK	DESCRIPTION		ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098UT/01.PRT	
CAD FILENAME/LAYERS		09V098UT_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (16) C-13 & (4) C-19 & (2) L6-30 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/-	
DRAWN BY MAV		SCALE NONE	
DATE 6-27-11		DRAWING NO. 09V098UT	
CHK'D KRKE		DWG B	