

Part Number: 9910
UL AWM Style 1015



Product Description

Tinned copper conductor, PVC insulation. Rated 105°C, 600V. Rated 2500V peak for electronic circuits, and internal wiring of electronic and electrical equipment.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors	No. of Pairs
10	65x28	TC - Tinned Copper	1	6
Total Number of Conductors:			1	

Insulation:

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.03 in

Color Chart 1:

Number
6

Outerjacket 1:

Nominal Diameter
0.18 mm

Electrical Characteristics

Conductor DCR:

Nominal Outer Shield DCR

6 Ohm/km

Use

Safety

CSA Flammability:	FT1
UL Flammability:	VW-1

Temperature Range

Mechanical Characteristics

Part Number

Standards

CA Prop 65 (CJ for Wire & Cable):	Yes
CSA Rating:	600V, 105°C
CSA Type:	AWM I A/B or TEW
MII Order #39 (China RoHS):	Yes
UL AWM Style:	MTW or TW or AWM 1015/1230
UL Rating:	600V, 105°C
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

History

Product Variants

Part Number	Color	Put-Up Type	Length
9910 002100	RED	Reel	100 ft
9910 0022000	RED	Reel	2000 ft
9910 002250	RED	Reel	250 ft
9910 004100	YELLOW	Reel	100 ft
9910 004250	YELLOW	Reel	250 ft
9910 009100	WHITE	Reel	100 ft
9910 0092000	WHITE	Reel	2000 ft
9910 009250	WHITE	Reel	250 ft
9910 010100	BLACK	Reel	100 ft
9910 0102000	BLACK	Reel	2000 ft
9910 010250	BLACK	Reel	250 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.