

NOTES:
1. IDENTIFICATION: 1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19, METERED
230V / 16A / SINGLE-PHASE POU

PANDUIT P/N	WEIGHT
HB1D2A0BA08W1	5.7 lb (2.7 kg)

<u>PART NO.</u>	<u>COLOR</u>
HB1D2A0BA08W1	BLACK

2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).




4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).

5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.


6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.


8. MAXIMUM AVAILABLE POWER = 3.7 KW



PLUG
16 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF



FOUR (4)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



FOUR (4)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

OOA	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098HC					
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH

MODEL FILENAME		09V098HC/00.PRT	
CAD FILENAME/LAYERS		09V098HC_DC/00A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19, METERED POWER OUTLET UNIT (HB1D2A0BA08W1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ALL DIMENSIONS ARE GIVEN IN	
X.X +/- 0.03	X. +/- 0.8	INCHES, THIRD ANGLE PROJECTION	
X.XX +/- 0.015	X.X +/- 0.4		
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO. 09V098HC	
CHK'D KRKE		DWG B	