

CIRRUS CR5-2U12

recording

2U 12-Bay Enterprise Video Server

The CIRRUS CR5-2U12 NVR enterprise video server has been designed for performance and peace of mind. Offering recording capacity up to 72TB, the CR5-2U12 offer key features such Quick Setup Wizard, configurable RAID levels, redundant power, SSD boot and dual Gigabit Ethernet.



Base Specifications


Processor	Intel® Xeon® E5-2620v3
Memory	16GB DDR4 2133MHz
Operating System	Windows Embedded 7
Drive Bays	12 x 3.5" (Hot-Swappable)
Drive Capacities	1TB, 2TB, 3TB, 4TB, 5TB, 6TB
Drive Interface	SATA or SAS
Max. Raw Storage	72TB
Hardware RAID	0,1,5,6,10,50,60
Boot Drive	128GB SSD SATA3
Dedicated Graphics	GeForce 210 1024MB DDR3
Video Outputs	HDMI, DVI, VGA
Max. Resolution	2560 x 1600
Power Supply	100-240V, 740W, Redundant
AC Input Frequency	50 ~ 60 Hz
Networking	2 x GbE + 1 x IPMI LAN
Accessories	USB Keyboard & Mouse
Form Factor	2U Rack, 25.5" Depth
Dimensions	3.5" x 17.2" x 25.5"
Operating Temp.	10°C - 35°C (50°F - 95°F)
Operating Humidity	8% - 90% (non-condensing)
Warranty	3 Years On Site NBD 8/5
Compliance	FCC, CE

Features

- Intel® Xeon® E5 Series Processor
- Up to 600 Mbps Recording Throughput
- Up to 72 TB (Configurable RAID)
- Designed for 24/7 Video Recording
- Dedicated Graphics Card
- Redundant Power Supply
- Pre-loaded VMS Software

Quick Setup Wizard

The CR5-2U12 is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which VMS software solution to deploy on your NVR appliance.



IONODES