

Part Number: 1078A

300V, (12 pr) 20 AWG (7x28), (1) 22 AWG (7x30) BC,

PVC/PVC, Foil Shld, PLTC-ER, CMG

Product Description

Twelve 20 AWG pairs stranded (7x28) bare copper condutors plus one 22 AWG stranded (7x30) bare copper conductor, twisted pairs, PVC insulation, individual plus an overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors	No. of Pairs
20	7x28	BC - Bare Copper		12
22	7×30	BC - Bare Copper	1	

Total Number of Conductors: 25

Insulation:

Material	Nominal Diameter
PVC - Polyvinyl Chloride	o.o68 in

Color Chart 1:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10
11	Black & White and Numbered 11
12	Black & White and Numbered 12
Communication Wire	Orange

Innershield:

Туре	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	22	7x30 mm
				TC - Tinned Copper	

Cabling 1:

Lay Direction	
Left Hand	

Outershield 1:

Туре	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	M100 %	TC - Tinned Copper	20	7x28 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.637 in	0.064 in	Yes

Print Legend: 105 OR	EGEND: BELDEN 1078A E34972 12PR20 1C22 SHIELDED (UL) CMG D5C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V R C(UL) CMGFT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL UMBER) FEET
----------------------	--

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	6.5 Ohm/1000ft

Capacitance:

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
30 pF/ft	55 pF/ft

Current:

Max. Recommended Current [A]

3 Amps per conductor @ 25°C

Inductance:

Nominal Indu	ctance
0.19 µH/ft	

Voltage:

UL Voltage Rating	
300 V RMS (PLTC	
CMG)	
150 V RMS (ITC)	

Use

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	468 lbs

Safety

C(UL) Flammability:	FT4
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL Flammability:	UL1685 FT4 Loading

Temperature Range

Operating Temp Range:	-30°C To +105°C
UL Temp Rating:	105°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	6.75 in
-----------------------------	---------

Part Number

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Product Variants

Part Number	Color	Put-Up Type	Length
1078A 0107500	BLACK	Reel	7500 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in comptiance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor?s inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden?s knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.