




700211279 | Z-012-DS-6F-FSUBK
Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored

Construction Materials

Fiber Type Solution	OptiSPEED®, 62.5 µm multimode fiber (OM1)
Total Fiber Count	12
Fiber Type	OptiSPEED®, 62.5 µm multimode fiber (OM1)
Fiber Type, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Cable Weight	33.0 lb/kft 49.0 kg/km
Diameter Over Jacket	7.20 mm 0.28 in

Physical Specifications

Minimum Bend Radius, loaded	10.8 cm 4.3 in
Minimum Bend Radius, unloaded	7.2 cm 2.8 in
Tensile Load, long term, maximum	120 lbf 534 N
Tensile Load, short term, maximum	400 lbf 1780 N
Vertical Rise, maximum	500.0 m 1640.4 ft

700211279 | Z012-DS-6F-FSUBK

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Installation Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	126 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze Test Method	IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-40 °C to +70 °C (-40 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696 EN 187105 Telcordia GR-20 (water penetration) Telcordia GR-409
-------------------------------	--

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-6F-TB (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable