

Part Number: 1095A

600V Tray, (12 triad) 18 AWG (7x26) BC, PVC-NYL/PVC,
Foil Shld, TC-ER

Product Description

Twelve 18 AWG triads stranded (7x26) bare copper conductors, twisted triads, PVC/Nylon insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Triads
18	7x26	BC - Bare Copper	12
Total Number of Conductors:			36

Insulation:

Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Color Chart 1:

Number	Color
1	Black printed #1
2	Black printed #2
3	Black printed #3
4	Black printed #4
5	Black printed #5
6	Black printed #6
7	Black printed #7
8	Black printed #8
9	Black printed #9
10	Black printed #10
11	Black printed #11
12	Black printed #12

Color Chart 2:

Number	Number
1	Black & White & Red and numbered 1
2	Black & White & Red and numbered 2
3	Black & White & Red and numbered 3
4	Black & White & Red and numbered 4
5	Black & White & Red and numbered 5
6	Black & White & Red and numbered 6
7	Black & White & Red and numbered 7
8	Black & White & Red and numbered 8
9	Black & White & Red and numbered 9
10	Black & White & Red and numbered 10
11	Black & White & Red and numbered 11
12	Black & White & Red and numbered 12

Stranding:

Lay Length	Twists
2.5 in	4.8 twist/ft

Innershield:

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	20	7x28 mm
				TC - Tinned Copper	

Cabling 1:

Lay Length	Twists
11 in	1.09 twist/ft

Outershield 1:

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	18	7x26 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.944 in	0.084 in	Yes

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Inner Shield DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	7.11 Ohm/1000ft	4 Ohm/1000ft

Capacitance:

Element	Nom. Capacitance Conductor to Shield	Nom. Mutual Capacitance
Individual	43 pF/ft	37 pF/ft
Overall	30 pF/ft	

Current:

Max. Recommended Current [A]
5 Amps per conductor @ 25°C

Voltage:

UL Voltage Rating
600 V RMS (NEC Type TC)
150 V RMS (NPLF)

Use

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	997 lbs

Safety

C(UL) Flammability:	FT4
IEEE Flammability:	1202
UL Flammability:	UL1685 UL Loading

Temperature Range

Dry Temp Range:	-30°C To +90 °C
Wet Temp Range:	-30°C To +75°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	9.75 in
-----------------------------	---------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
Other Specification:	Other Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Notes:	Triad groups are numbered for ease of identification. Alternate color coding available upon request.
--------	--

Product Variants

Part Number	Color	Put-Up Type	Length
1095A 0102500	BLACK	Reel	2500 ft
1095A 0104000	BLACK	Reel	4000 ft
1095A 0105000	BLACK	Reel	5000 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.