




760127340 | R-048-DZ-8W-FMUYL

**Riser Distribution Cable, interlocking aluminum armored with riser jacket, 48 fiber multi-unit with 12 fiber subunits**

## Representative Image



## General Specifications

Cable Type	Distribution
Construction Type	Armored
Subunit Type	Gel-free

## Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Total Fiber Count	48
Armor Type	Interlocking aluminum
Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Fiber Type, quantity	48
Fibers per Subunit, quantity	12
Jacket Color	Yellow

## Dimensions

Buffer Tube/Subunit Diameter	5.95 mm   0.23 in
Cable Weight	294.0 lb/kft   438.0 kg/km
Diameter Over Armor	20.96 mm   0.83 in
Diameter Over Jacket	23.00 mm   0.91 in
Subunit, quantity	4

## Physical Specifications

Minimum Bend Radius, loaded	46.0 cm   18.1 in
-----------------------------	-------------------

760127340 | R-048-DZ-8W-FMUYL

Minimum Bend Radius, unloaded	32.2 cm		12.7 in
Tensile Load, long term, maximum	90 lbf		400 N
Tensile Load, short term, maximum	300 lbf		1335 N
Vertical Rise, maximum	93.0 m		305.1 ft

## Flame Test Specifications

Flame Test Listing	NEC OFCR (ETL) and c(ETL)
Flame Test Method	UL 1666

## Environmental Specifications

Environmental Space	Riser
Installation Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## Mechanical Test Specifications

Compression	485 lb/in		85 N/mm
Compression Test Method	FOTP-41		IEC 60794-1 E3
Flex	25 cycles		
Flex Test Method	FOTP-104		IEC 60794-1 E6
Impact	25.80 ft lb		35.00 N-m
Impact Test Method	FOTP-25		IEC 60794-1 E4
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1 E1
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1 E7

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
-------------------------------	---------------------------------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

## \* Footnotes

---

Operating Temperature Specification applicable to non-terminated bulk fiber cable