



760128850 | HTK-19-DS-2U
Horizontal Trough Kit, 19 in rack mountable, double sided, 2 RU

Dimensions

Depth	359.2 mm 14.1 in
Height	88.1 mm 3.5 in
Width	482.6 mm 19.0 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Color	Black
Configuration Type	Double-sided
Product Type	Horizontal cable management
Rack Units	2
Cover, quantity	2
Finish	Powder-coated, smooth
Includes	Four #12-24 x 1/2 in screws Instruction sheet
Package Quantity	1
Packaging Type	Assembled

Mechanical Specifications

Material Type	Aluminum Plastic Steel
---------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

