

 **Part Number:** 7924A

Cat 5e Flex DataTuff®, (4 pr) 24 AWG (7x32) TC,
PO/PVC, CMR, CMX-Outdoor

Product Description

Four Cat 5e 24 AWG Bonded-Pairs stranded (7x32) tinned copper conductors, polyolefin insulation, PVC jacket.

Product Specifications

Technical Specifications

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, 350MHz Enhanced Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, CMX - Outdoor, RJ-45 Compatible, Flexible Applications
-------------------------------	--

Construction and Dimensions

Conductor:

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.022 in	4
Total Number of Conductors:			8	

Insulation:

Material	Nominal Diameter	Nominal Wall Thickness
PO - Polyolefin	0.042 in	0.008 in

Color Chart 1:

Number	Color
1	White/Orange Stripe & Orange
2	White/Blue Stripe & Blue
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outershield 1:

Material
Unshielded

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness
Industrial Grade PVC - Polyvinyl Chloride	0.242 in	0.03 in

Electrical Characteristics

Conductor DCR:

Max. Conductor DCR	Max. DCR Unbalance
9 Ohm/1000ft	3 %

Capacitance:

Max. Capacitance Unbalance	Nom.Mutual Capacitance
66 pF/ft	15 pF/ft

Delay:

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
510 ns/100m	25 ns/100m	70 %

High Freq:

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.4 db/100m	65.3 dB	65.3 dB	62.9 dB	63.8 dB	60.8 dB	20 dB	100 ± 12 Ohm	
4 MHz	4.8 db/100m	56.3 dB	56.3 dB	51.5 dB	51.7 dB	48.7 dB	23 dB	100 ± 12 Ohm	
8 MHz	6.8 db/100m	51.8 dB	51.8 dB	45 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 12 Ohm	
10 MHz	7.7 db/100m	50.3 dB	50.3 dB	42.6 dB	43.8 dB	40.8 dB	25 dB	100 ± 12 Ohm	
16 MHz	9.7 db/100m	47.3 dB	47.3 dB	37.5 dB	39.7 dB	36.7 dB	25 dB	100 ± 12 Ohm	
20 MHz	11 db/100m	45.8 dB	45.8 dB	34.8 dB	37.7 dB	34.7 dB	25 dB	100 ± 12 Ohm	
25 MHz	12.4 db/100m	44.3 dB	44.3 dB	31.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15 Ohm	
31.25 MHz	13.9 db/100m	42.9 dB	42.9 dB	29 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15 Ohm	
62.5 MHz	20.2 db/100m	38.4 dB	38.4 dB	18.3 dB	27.8 dB	24.8 dB	21.5 dB	100 ± 15 Ohm	
100 MHz	26 db/100m	35.3 dB	35.3 dB	9.2 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 18 Ohm	100 ± 10 Ohm
155 MHz	33.2 db/100m	32.5 dB	32.5 dB	0 dB	19.9 dB	16.9 dB	19 dB	100 ± 18 Ohm	100 ± 10 Ohm
200 MHz	38.4 db/100m	30.8 dB	30.8 dB		17.7 dB	14.7 dB	19 dB	100 ± 20 Ohm	100 ± 10 Ohm
250 MHz	43.7 db/100m	29.3 dB	29.3 dB		15.8 dB	12.8 dB	18 dB	100 ± 20 Ohm	100 ± 10 Ohm
300 MHz	48.6 db/100m	28.2 dB	28.2 dB		14.2 dB	11.2 dB	18 dB	100 ± 20 Ohm	100 ± 10 Ohm
310 MHz	49.5 db/100m	27.9 dB	27.9 dB		13.9 dB	10.9 dB	18 dB	100 ± 20 Ohm	100 ± 10 Ohm
350 MHz	53.2 db/100m	27.2 dB	27.2 dB		12.9 dB	9.9 dB	17 dB	100 ± 22 Ohm	100 ± 10 Ohm
1 MHz									
4 MHz									
8 MHz									
10 MHz									
16 MHz									
20 MHz									
25 MHz									
31.25 MHz									
62.5 MHz									
100 MHz									
155 MHz									
200 MHz									
250 MHz									
300 MHz									
310 MHz									
350 MHz									

Voltage:

UL Voltage Rating

300 V RMS

Use

Suitability - Oil Resistance:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	40 lbs

Safety

CSA Flammability:	FT4
UL Flammability:	UL1666 Riser

Temperature Range

Installation Temp Range:	-25°C To +75 °C
Operating Temp Range:	-40°C To +75°C
Storage Temp Range:	-25°C To +75 °C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	0.25 in
-----------------------------	---------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

ISO/IEC Compliance:	Other Standards
Telecommunications Standards:	Telecommunications Standards
CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
Other Specification:	Other Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

History

Notes:	US Patents 5, 606, 151; 5, 734, 126; 5, 763, 823. EtherNet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.
--------	--

Product Variants

Part Number	Color	Put-Up Type	Length
7924A 0021000	RED	Reel	1000 ft
7924A 0061000	BLUE	Reel	1000 ft
7924A 0081000	GRAY	Reel	1000 ft
7924A 0101000	BLACK	Reel	1000 ft
7924A 0102000	BLACK	Reel	2000 ft
7924A 1NH1000	TEAL	Reel	1000 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.