




700212020 | 1071E RD 4/23 W1000
GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, red jacket, 4 pair count, 1000 ft (305 m) length, WE TOTE® box

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin
Separator Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	25.60 lb/kft
Diameter Over Jacket	5.893 mm 0.232 in
Jacket Thickness	0.559 mm 0.022 in

Electrical Specifications

ANSI/TIA Category	6
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	7.61 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	300 MHz
Operating Voltage, maximum	80 V

700212020 | 1071E RD 4/23 W1000

Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMG CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
UL Temperature Rating	75 °C 167 °F

General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	WE TOTE® box
Brand	GigaSPEED XL® SYSTIMAX®
Jacket Color	Red
Product Number	1071E
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Ordering Note	Not available in Europe, the Middle East, or Africa
Separator Type	Bisector

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
--------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

