



760093336 | 360-iP-HD-2U-IP-SD
SYSTIMAX 360™ iPatch® G2 High Density Sliding Fiber Shelf

Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+) LazrSPEED® 300, 50 µm multimode fiber (OM3) LazrSPEED® 550, 50 µm multimode fiber (OM4) OptiSPEED®, 62.5 µm multimode fiber (OM1) TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Material Type	ABS Polycarbonate

Dimensions

Depth	323.85 mm 12.75 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in
Weight	4.81 kg 10.60 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	CE cUL UL ACMA
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	SYSTIMAX 360™ SYSTIMAX® iPatch®
Intelligence Type	iPatch® enabled
Product Type	Shelf
Shelf Movement	Sliding
Color	Black Cool gray
Interface	MPO
Package Quantity	1
Total Ports, quantity	72

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

