




760105825 | 1091B YL 4/23 R1000
GigaSPEED X10D® 1091B ETL Verified Category 6A U/UTP Cable, yellow jacket, 4 pair count, 1000 ft (305 m) length, reel

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin
Separator Material	Polyolefin
Separator 2 Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	37.30 lb/kft
Diameter Over Jacket	7.239 mm 0.285 in
Jacket Thickness	1.295 mm 0.051 in

Electrical Specifications

ANSI/TIA Category	6A
Characteristic Impedance	100 ohm
Characteristic Impedance Tolerance	±15 ohm
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	7.61 ohms/100 m
Mutual Capacitance	6.0 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	65 %

760105825 | 1091B YL 4/23 R1000

Operating Frequency, maximum	550 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
UL Temperature Rating	75 °C 167 °F

General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	Reel
Brand	GigaSPEED X10D® SYSTIMAX®
Jacket Color	Yellow
Product Number	1091B
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Separator Type	Isolator

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
--------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

