



760168443 | 360G2-iP-96F-LC-SD-KIT-5PK
SYSTIMAX 360™ iPatch® 96F-LC, Sliding Shelf 5PK Kit

Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+) LazrSPEED® 300, 50 µm multimode fiber (OM3) LazrSPEED® 550, 50 µm multimode fiber (OM4) OptiSPEED®, 62.5 µm multimode fiber (OM1) TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Material Type	ABS Polycarbonate

Dimensions

Depth	17.78 mm 0.70 in
Height	28.19 mm 1.11 in
Width	194.31 mm 7.65 in
Weight	0.11 kg 0.25 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	SYSTIMAX 360™ iPatch®
Intelligence Type	iPatch® enabled
Product Type	Shelf, preterminated
Color	Cool gray
Interface	LC
Package Quantity	5
Total Ports, quantity	240

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU
ISO 9001:2008

Classification