



**Part Number:** 1012A

Thermocouple Extension, (4 pr) 20 AWG Solid Type KX, PVC/PVC, Foil Shld, CMG

## Product Description

Four 20 AWG pairs solid Type KX conductors, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

## Product Specifications

## Technical Specifications

### Construction and Dimensions

#### Conductor:

AWG	Stranding	Material	No. of Pairs
20	Solid	Chromel	2
20	Solid	Alumel	2
Total Number of Conductors:			9

#### Insulation:

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.016 in

#### Color Chart 1:

Number	Color
1	Yellow & Red and Numbered 1
2	Yellow & Red and Numbered 2
3	Yellow & Red and Numbered 3
4	Yellow & Red and Numbered 4

Innershield:

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	22	7x30 mm
				TC - Tinned Copper	

Outershield 1:

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outerjacket 1:

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.383 in	Yes

Print Legend:

BELDEN 1012A E34972 4PR20 1C22 THCPL EXTN KX SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG ---- FT4 IEEE1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET

Electrical Characteristics

Conductor DCR:

Individual Pair Nominal Shield DCR	Nominal Outer Shield DCR
10.6 Ohm/1000ft	6.8 Ohm/1000ft

Use

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	159 lbs

Safety

UL Flammability:	UL1685 FT4 Loading
------------------	--------------------

Temperature Range

Non-UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	3.9 in
-----------------------------	--------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

ANSI Compliance:	ANSI Specification
CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
CSA AWM Specification:	CSA Specification
IEEE Specification:	IEEE Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Notes:	Chromel & Alumel = "Chromel and Alumel are Hoskins Manufacturing Company trademarks."
--------	---

Product Variants

Part Number	Color	Put-Up Type	Length
1012A 0045000	YELLOW	Reel	5000 ft

© 2016 Belden, Inc.

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.