

**Part Number:** 82743

Audio/Control/Instrumentation, (6 pr) 22 AWG (7x30)  
TC, FEP/LS PVC, CMP

## Product Description

Six 22 AWG pairs stranded (7x30) tinned copper conductors, plenum, twisted pairs, Teflon® (FEP) insulation, Flamarrest® jacket.

## Product Specifications

## Technical Specifications

### Construction and Dimensions

#### Conductor:

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	6
Total Number of Conductors:			12

#### Insulation:

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.007 in

#### Color Chart 1:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown

#### Outershield 1:

Material
Unshielded

#### Outerjacket 1:

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.238 in	0.015 in

## Electrical Characteristics

### Conductor DCR:

Nominal Conductor DCR
16 Ohm/1000ft

### Capacitance:

Nom. Capacitance Conductor to Conductor
21 pF/ft

### Impedance:

Nominal Characteristic Impedance
80 Ohm

### Current:

Max. Recommended Current [A]
3.3 Amps per conductor @ 25°C (10°C rise in temp)

### Inductance:

Nominal Inductance
0.15 µH/ft

### Voltage:

UL Voltage Rating
300 V RMS

## Use

Max Recommended Pulling Tension:	109 lbs
----------------------------------	---------

## Safety

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262

## Temperature Range

Operating Temp Range:	0°C To +75°C
-----------------------	--------------

Mechanical Characteristics

Min Bend Radius/Minor Axis:	2.5 in
-----------------------------	--------

Part Number

Plenum (Y/N):	Yes
---------------	-----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Product Variants

Part Number	Color	Put-Up Type	Length
82743 8771000	NATURAL	Reel	1000 ft

© 2016 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.