



**Part Number:** 3082A

DeviceNet™, (1 pr) 15 AWG (19x28) TC, (1 pr) 18 AWG (19x30) TC, PVC-FPE/PVC, Foil+TC Braid Shld, CMG, PLTC-ER

## Product Description

One 15 AWG stranded (19x28) tinned copper conductors, one 18 AWG stranded (19x30) tinned copper conductors, PVC insulation (power), foam polyethylene (FPE) insulation (data), individual foil shield (100% coverage) plus an overall tinned copper braid (65% coverage), PVC jacket.

## Product Specifications

## Technical Specifications

## Construction and Dimensions

### Conductor:

AWG	Stranding	Material	No. of Pairs
15	19x28	TC - Tinned Copper	1
18	19x30	TC - Tinned Copper	1
<b>Total Number of Conductors:</b>			4

### Insulation:

Element	Material
15	PVC - Polyvinyl Chloride
18	FPE - Foam Polyethylene

### Color Chart 1:

Number	Color
1 (15 AWG)	Red & Black
2 (18 AWG)	Blue & White

**Stranding:**

Lay Length
1 MHz

**Innershield:**

Type	Layer	Material	Coverage [%]
Tape	15 AWG Pair	Aluminum Foil-Polyester Tape	100 %
Tape	18 AWG Pair	Aluminum Foil-Polyester Tape	100 %

**Outershield 1:**

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Braid	TC - Tinned Copper	65 %	TC - Tinned Copper	18	19x30 mm

**Outerjacket 1:**

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.48 in	0.06 in

**Electrical Characteristics****Conductor DCR:**

Element	Nominal Conductor DCR	Nominal Outer Shield DCR
15 AWG	3.6 Ohm/1000ft	1.8 Ohm/1000ft
18 AWG	6.9 Ohm/1000ft	

**Capacitance:**

Element	Nom. Capacitance Conductor to Conductor
18 AWG Pair Only	12 pF/ft

**Delay:**

Max. Delay	Max. Delay Description	Nominal Velocity of Propagation (VP) [%]	Nominal Velocity of Propagation (VP) Description
1.36 ns/ft	18 AWG Pair Only	75 %	18 AWG Pair Only

**High Freq:**

Element	Frequency [MHz]	Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
18 AWG Pair Only		0.13 db/100ft	120 Ohm
18 AWG Pair Only		0.25 db/100ft	
		0.36 db/100ft	
	0.125 MHz		
	0.5 MHz		
	1 MHz		

## Current:

Element	Max. Recommended Current [A]
15 AWG	8.0 Amps
18 AWG	5.0 Amps

## Inductance:

Element	Nominal Inductance
15 AWG Pair Only	0.174 $\mu$ H/ft

## Voltage:

UL Voltage Rating
300 V RMS (CL2, CMG)
600 V RMS (UL AWM Style 20201)
300 V RMS (C(UL) AWM)

## Use

Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	190 lbs

## Safety

CSA Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading

## Temperature Range

Operating Temp Range:	-20°C To +75°C
UL Temp Rating:	75°C

## Mechanical Characteristics

Min Bend Radius/Minor Axis:	4.8 in
-----------------------------	--------

## Part Number

Plenum (Y/N):	No
---------------	----

## Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification

<b>MII Order #39 (China RoHS):</b>	MII Order #39 (China RoHS)
<b>NEC/(UL) Specification:</b>	NEC/(UL) Specification
<b>Other Specification:</b>	Other Specification
<b>UL AWM Style:</b>	AWM Specification
<b>EU Directive Compliance:</b>	EU Directive 2003/11/EC (BFR)
<b>EU CE Mark:</b>	EU CE Mark

## History

<b>Notes:</b>	Thick. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Associatio, Inc. Trademark. Jacket printed "1PR16" instead of "1PR15" due to UL requirements for CMG Listing.
---------------	---

## Product Variants

Part Number	Color	Put-Up Type	Length
3082A			
3082A T5U2000	GRAY T5U	Reel	2000 ft
3082A T5U3000	GRAY T5U	Reel	3000 ft
3082A T5U500	GRAY T5U	Reel	500 ft
3082A			

© 2016 Belden, Inc.

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.