



**Part Number:** 7200A

300V Flex Data, (1 pr) 24 AWG (41x40) BC + Grd, FPE-PE/PVC, Foil + TC Braid Shld, CM

## Product Description

One 24 AWG pair stranded (41x40) bare copper conductors, twisted pairs, foam polyethylene insulation with skin, overall Beldfoil® shield (100% coverage) plus tinned copper braid shield (85% coverage), 24 AWG stranded (41x40) tinned copper drain wire, oil-resistant PVC jacket.

## Product Specifications

## Technical Specifications

<b>Suitable Applications:</b>	Flex Data, RS232, RS485
-------------------------------	-------------------------

## Construction and Dimensions

### Conductor:

AWG	Stranding	Material	No. of Pairs
24	41x40	BC - Bare Copper	1

<b>Total Number of Conductors:</b>	2
------------------------------------	---

### Insulation:

Material
FPE - Foam Polyethylene
PE - Polyethylene

### Color Chart 1:

Number	Color
1	White & Blue

## Outershield 1:

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	41x40 mm
Braid	2	TC - Tinned Copper		85 %			

## Outerjacket 1:

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.24 in

## Electrical Characteristics

### Capacitance:

Max. Capacitance Conductor to Conductor	
15 pF/ft	
Min Insulation Resistance:	6.1 Megaohms/1,000 ft. minimum MOhm*1000ft

### Impedance:

Max. Differential Impedance (1MHz)
120 +/-15

### Delay:

Nominal Velocity of Propagation (VP) [%]
72 %

### Voltage:

UL Voltage Rating
300 V RMS

## Use

Suitability - Oil Resistance:	Yes
Flex Cycle Rating:	1 Million
Max Recommended Pulling Tension:	41 lbs

## Safety

UL Flammability:	UL1685 UL Loading
------------------	-------------------

## Temperature Range

Operating Temp Range:	-20°C To +60°C
UL Temp Rating:	60°C

## Mechanical Characteristics

Min Bend Radius (Continuous Flexing):	3.6 in
Min Bend Radius/Minor Axis:	2.6 in

## Part Number

Plenum (Y/N):	No
---------------	----

## Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
Other Specification:	Other Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

## History

Notes:	1 million flex cycles based on proper installation techniques in a C-track cable guide.
--------	---

## Product Variants

Part Number	Color	Put-Up Type	Length
7200A X4P1000	GREEN X4P	Reel	1000 ft
7200A X4P500	GREEN X4P	Reel	500 ft
7200A			

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.