



Part Number: 8624

Audio/Control/Instrumentation, (19) 16 AWG (19x29)

TC, PVC/PVC

# **Product Description**

Nineteen 16 AWG stranded (19x29) tinned copper conductors, conductors cabled, PVC insulation, PVC jacket.

# **Product Specifications**

# **Technical Specifications**

# **Construction and Dimensions**

#### Conductor:

AWG	Stranding	Material	No. of Conductors	
16	16 19x29 TC - Tinned Copper		19	
Total Num	ber of Conductors:	19	9	

#### Insulation:

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.031 in

#### Color Chart 1:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black
10	Orange/Black
11	Blue/Black
12	Black/White
13	Red/White
14	Green/W hite
15	Blue/White
16	Black/Red
17	White/Red
18	Orange/Red
19	Blue/Red

#### Outershield 1:

Material

Unshielded

# Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.74 in	0.065 in

# **Electrical Characteristics**

### **Conductor DCR:**

**Nominal Conductor DCR** 

4.4 Ohm/1000ft

#### Capacitance:

Nom. Capacitance Conductor to Conductor

19.5 pF/ft

#### **Current:**

#### Max. Recommended Current [A]

3.5 Amps per conductor @ 25°C

#### Voltage:

#### Non-UL Voltage Rating

600 V RMS

### Use

Max Recommended Pulling Tension:	577 lbs
F 1-111 1-12 1-13 1-13 1-13 1-13 1-13 1-1	377

# Safety

ther Flammability:	VW-1, FT1
--------------------	-----------

# **Temperature Range**

Operating Temp Range:	-20°C To +80°C
UL Temp Rating:	80°C

# **Mechanical Characteristics**

# **Part Number**

# **Standards**

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)	
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)	
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)	
EU CE Mark:	EU CE Mark	

### History

# **Product Variants**

Part Number	Color	Put-Up Type	Length
8624 0601000	CHROME	Reel	1000 ft
8624 060500	CHROME	Reel	500 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of

such information and specifications does not ensure product availability

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.