



Part Number: 8692

Audio/Control/Instrumentation, (9 pr) 18 AWG (16x30) TC, PVC/PVC, CMG

Product Description

Nine 18 AWG pairs stranded (16x30) tinned copper conductors, twisted pairs, PVC insulation, PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material		No. of Pairs
18	16×30	TC - Tinned Coppe	r	9
Total Number of (Conductors:		18	

Insulation:

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.013 in

Color Chart 1:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White
9	Red & Green

Innershield:

Material		
Unshielded		

Outershield 1:

Material	
Unshielded	

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.524 in	0.04 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	
5.8 Ohm/1000ft	

Capacitance:

Nom. Capacitance Conductor to Conductor	
30 pF/ft	

Current:

Max. Recommended Current [A]	
2.6 Amps per conductor @ 25°C	

Inductance:

Nominal Inductance	
0.17 µH/ft	

Voltage:

UL Voltage Rating	
300 V RMS	

Use

Max Recommended Pulling Tension:	364 lbs

Safety

CSA Flammability:	FT4

Temperature Range

Non-UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	5.25 in

Part Number

Plenum (Y/N):	No

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)	
CEC/C(UL) Specification:	CEC/C(UL) Specification	
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)	
NEC/(UL) Specification:	NEC/(UL) Specification	
UL AWM Style:	AWM Specification	
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)	
EU CE Mark:	EU CE Mark	

History

Product Variants

Part Number	Color	Put-Up Type	Length
8692 0601000	CHROME	Reel	1000 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of

such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will, Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor?s inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden?s knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Part # PF_8692 | Page 4 of 4 | July 08, 2016 Belden Inc. | belden.catalog.belden.com/en/Products/Detail/PF_8692