



Part Number: 9463
Blue Hose® Cable

Product Description

20 AWG stranded (7x28) .038" tinned copper conductors, polyethylene insulation, Beldfoil® (100%; coverage) plus a tinned copper braid shield (55%; coverage), sunlight-resistant PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
20	7x28	TC - Tinned Copper	0.038 in	1
Total Number of Conductors:			2	

Insulation:

Material	Nominal Diameter
PE - Polyethylene	0.078 in

Color Chart 1:

Number	Color
1	Clear & Blue

Stranding:

Twists	Diameter
2.75 twist/ft	0.154 mm

Outersheild 1:

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	20	7x28H mm
Braid	2	TC - Tinned Copper		55 %			

Outerjacket 1:

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.238 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	4.1 Ohm/1000ft

Capacitance:

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
19.7 pF/ft	36 pF/ft

Other Electrical Characteristic 1:	DC Resistance Unbalanced: .77 Ohms/1000 ft Max
---	--

Impedance:

Nominal Characteristic Impedance
78 Ohm

High Frequency (Nominal/Typical):

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 db/100m
10 MHz	2.1 db/100m
50 MHz	5 db/100m
100 MHz	7.5 db/100m
200 MHz	11 db/100m
400 MHz	16 db/100m

Delay:

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	1.54 ns/ft	66 %

High Freq:

Frequency [MHz]
1 MHz
10 MHz
50 MHz
100 MHz
200 MHz
400 MHz

Inductance:

Nominal Inductance
0.12 μ H/ft

Voltage:

UL Voltage Rating
300V RMS (UL AWM Style 2464)
300 (NEC Type CM) V RMS
300V RMS (NEC Type CL2)

Use

Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	48 lbs

Safety

UL Flammability:	UL1685 UL Loading
------------------	-------------------

Temperature Range

Operating Temp Range:	-40°C To +80°C
UL Temp Rating:	80°C (UL AWM Style 2464)

Mechanical Characteristics

Min Bend Radius/Minor Axis:	2.4 in
-----------------------------	--------

Part Number

Plenum Number:	89463
----------------	-------

Standards

CA Prop 65 (CJ for Wire & Cable):	Yes
CEC/C(UL) Specification:	CM

Customer Part Number Reference Spec:	Allen Bradley P/N 1770-CD
MII Order #39 (China RoHS):	Yes
NEC/(UL) Specification:	CL2^CM
PMSHA Specification:	P-7K-SC-182141
UL AWM Style:	UL Style 2464 (300V 80°C)
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

History

Product Variants

Part Number	Color	Put-Up Type	Length
9463	BROWN	Reel	10000 ft
9463	BROWN	Reel	10000 ft
9463 00110000	BROWN	Reel	10000 ft
9463	BROWN	Reel	1000 ft
9463	BROWN	Reel	1000 ft
9463 0011000	BROWN	Reel	1000 ft
9463	BROWN	Reel	2000 ft
9463 00112000	BROWN	Reel	2000 ft
9463	BROWN	Reel	6000 ft
9463 0016000	BROWN	Reel	6000 ft
9463	ORANGE	Reel	10000 ft
9463 00310000	ORANGE	Reel	10000 ft
9463	ORANGE	Reel	1000 ft
9463	ORANGE	Reel	1000 ft
9463 0031000	ORANGE	Reel	1000 ft
9463	ORANGE	Reel	2000 ft
9463 00312000	ORANGE	Reel	2000 ft
9463	ORANGE	Reel	6000 ft
9463	ORANGE	Reel	6000 ft
9463 0036000	ORANGE	Reel	6000 ft
9463	VIOLET	Reel	1000 ft
9463	VIOLET	Reel	1000 ft
9463 0071000	VIOLET	Reel	1000 ft
9463	VIOLET	Reel	6000 ft
9463	VIOLET	Reel	6000 ft

9463 0076000	VIOLET	Reel	6000 ft
9463	BLUE, STRONG	Reel	1000 ft
9463	BLUE, STRONG	Reel	1000 ft
9463 J221000	BLUE, STRONG	Reel	1000 ft
9463	BLUE, STRONG	Reel	100 ft
9463	BLUE, STRONG	Reel	100 ft
9463 J22100	BLUE, STRONG	Reel	100 ft
9463	BLUE, STRONG	Reel	2000 ft
9463	BLUE, STRONG	Reel	2000 ft
9463 J2212000	BLUE, STRONG	Reel	2000 ft
9463	BLUE, STRONG	Reel	500 ft
9463	BLUE, STRONG	Reel	500 ft
9463 J22500	BLUE, STRONG	Reel	500 ft
9463	BLUE, STRONG	Reel	6000 ft
9463	BLUE, STRONG	Reel	6000 ft
9463 J226000	BLUE, STRONG	Reel	6000 ft
9463	BLUE, STRONG		1000 ft
9463	BLUE, STRONG		6000 ft
9463	BLUE, STRONG	UnReel	1000 ft
9463	BLUE, STRONG	UnReel	1000 ft
9463 J22U1000	BLUE, STRONG	UnReel	1000 ft
9463	BLUE, STRONG	UnReel	500 ft
9463	BLUE, STRONG	UnReel	500 ft
9463 J22U500	BLUE, STRONG	UnReel	500 ft
9463	BLACK	Reel	1000 m
9463.001829	BLACK	Reel	1829 m
9463.00305	BLACK	Reel	305 m
9463	BLACK	Reel	30 m
9463.00U152	BLACK	UnReel	152 m
9463.00U305	BLACK	UnReel	305 m
9463.01152	BLACK	Reel	152 m
9463	BLACK	Reel	3050 m
9463.02305	BLACK	Reel	305 m
9463.031829	BLACK	Reel	1829 m
9463.03305	BLACK	Reel	305 m
9463.041829	BLACK	Reel	1829 m
9463.04305	BLACK	Reel	305 m
9463	BLACK		305 m

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.