

Part Number: 1048A

600V Tray, (2 pr) 18 AWG (7x26) BC, PVC-NYL/PVC, Foil

Shld, TC-ER

Product Description

Two 18 AWG pairs stranded (7x26) bare copper conductors, twisted pairs, PVC/Nylon insulation, individually shielded plus an overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

18 7x26 BC - Bare Copper 2	

Insulation:

Material

PVC/Nylon - Polyvinyl Chloride/Nylon

Color Chart 1:

Number	Color
1	Black & White Numbered 1
2	Black & White Numbered 2

Innershield:

Туре	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	20	7x28 mm
				TC - Tinned Copper	

Cabling 1:

Lay Length	
4 in	

Outershield 1:

Туре	e Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	18	7x26 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.379 in	o.o48 in	Yes

Electrical Characteristics

Conductor DCR:

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
7.46 Ohm/1000ft	5.86 Ohm/1000ft	4.91 Ohm/1000ft

Voltage:

UL Voltage Rating	
600 V RMS (NEC Type TC)	
150 V RMS (NPLF)	

Use

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	140 lbs

Safety

C(UL) Flammability:	FT4
IEEE Flammability:	1202
UL Flammability:	UL1685 UL Loading

Temperature Range

Dry Temp Range:	-30°C To +90 °C
Wet Temp Range:	-30°C To +75 °C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	3.8 in
-----------------------------	--------

Part Number

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)	
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)	
C/(UL) Specification: NEC/(UL) Specification		
Other Specification:	Other Specification	
EU Directive Compliance:	pmpliance: EU Directive 2003/11/EC (BFR)	
EU CE Mark:	EU CE Mark	

History

Notes:		Alternate color coding available upon request.
--------	--	--

Product Variants

Part Number	Color	Put-Up Type	Length
1048A 0107500	BLACK	Reel	7500 ft

© 2016 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in comptiance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor?s inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden?s knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.