



Part Number: 9513

300V Power-Limited Tray Cable

Product Description

22 AWG pairs stranded (7x30) tinned copper conductors, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	3
Total Number of Conductors:			6

Insulation:

Material	Nominal Diameter
F-R PVC - Flame Retardant Polyvinyl Chloride	0.062 in

Color Chart 1:

Number	Color
1	Black & Red and Numbered
2	Black & Red and Numbered
3	Black & Red and Numbered

Outersheild 1:

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
F-R PVC - Flame Retardant Polyvinyl Chloride	0.324 in	0.042 in	Yes

Print Legend:	LEGEND: BELDEN 9513 E34972 3PR22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL)
---------------	--

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Outer Shield DCR
15 Ohm/1000ft	15 Ohm/1000ft

Capacitance:

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
26 pF/ft	45 pF/ft

Current:

Max. Recommended Current [A]
3.4 Amps per conductor @ 25°C A

Inductance:

Nominal Inductance
0.21 µH/ft

Voltage:

UL Voltage Rating
300V RMS

Use

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	63 lbs

Safety

C(UL) Flammability:	FT4
ICEA Flammability:	T-29-520

IEEE Flammability:	1202
UL Flammability:	UL1685 FT4 Loading

Temperature Range

Operating Temp Range:	-30°C To +105°C
UL Temp Rating:	105°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	3.3 in
-----------------------------	--------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	Yes
CEC/C(UL) Specification:	CMG
MII Order #39 (China RoHS):	Yes
NEC/(UL) Specification:	PLTC^ITC^CMG
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

History

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.