

Part Number: 1476A

300V, (8 pr) 18 AWG (7x26) BC, (1) 22 AWG (7x30) BC,
PVC/PVC, Foil Shld, PLTC-ER, CMG

Product Description

Eight 18 AWG pairs stranded (7x26) bare copper conductors, one 22 AWG stranded (7x30) bare copper conductor, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors	No. of Pairs
18	7x26	BC - Bare Copper		8
22	7x30	BC - Bare Copper	1	
Total Number of Conductors:			17	

Insulation:

Material
PVC - Polyvinyl Chloride

Color Chart 1:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 7
7	Black & White and Numbered 7
8	Black & White and Numbered 8
Communication	Orange

Innershield:

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	20	7x28 mm
				TC - Tinned Copper	

Outershield 1:

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	18	7x26 mm

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.586 in	0.053 in	Yes

Print Legend:	BELDEN 1476A E34972 8PR18 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG---FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
----------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Electrical Characteristics

Conductor DCR:

Element	Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
18 AWG	10.3 Ohm/1000ft	5.86 Ohm/1000ft	4.47 Ohm/1000ft
22 AWG		14.7 Ohm/1000ft	

Current:

Max. Recommended Current [A]
2.5 Amps per conductor @ 25°C

Voltage:

UL Voltage Rating
300 V RMS

Use

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	501 lbs

Safety

CSA Flammability:	FT4
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL Flammability:	UL1685 FT4 Loading

Temperature Range

Operating Temp Range:	-30°C To +105°C
-----------------------	-----------------

Mechanical Characteristics

Min Bend Radius/Minor Axis:	6 in
-----------------------------	------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CEC/C(UL) Specification:	CEC/C(UL) Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Notes:	Alternate color coding available upon request.
--------	------------------------------------------------

Product Variants

Part Number	Color	Put-Up Type	Length
1476A 0061000	BLUE, LIGHT	Reel	1000 ft
1476A 0105000	BLACK	Reel	5000 ft

© 2016 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.