

Part Number: 19230

Portable Cordage, (3) 16 AWG (26x30) BC,

EPDM/Rubber, Type SJO

Product Description

Three 16 AWG stranded (65x34) bare copper conductors, EPDM insulation, rubber jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

16 26x30 BC - Bare Copper 3	A۱	wg	Stranding	Material	No. of Conductors
2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2	16		26x30	BC - Bare Copper	3

Total Number of Conductors:	3
Type of Cordage:	SJO

Insulation:

Material	Nominal Wall Thickness
Rubber	0.031 in

Color Chart 1:

Color	
Black	
White	
Green	

Stranding:

Lay Length	
Black mm	

Cabling 1:

Filler	
Jute	

Outershield 1:

	ria	

Unshielded

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
Rubber	o.353 in	0.044 in	Paper Tape

Print Legend: 16-3 SJO 90°C (UL) E3462 - - - - CSA LL7874 16-3 SJO 90°C FT2

Electrical Characteristics

Current:

Max. Recommended Current [A] 13 Amps per conductor @ 25°C 10 Amps per conductor @ 25°C (over 50 ft.)

Voltage:

Dielectric Withstand Voltage	UL Voltage Rating
2000 V AC Applied For 1 Min.	300 V RMS

Use

Safety

CSA Flammabi	lity:	FT2

Temperature Range

Mechanical Characteristics

Part Number

Plenum (Y/N):	Plenum (Y/N):	No
---------------	---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CSA AWM Specification:	CSA Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

EU CE Mark:	EU CE Mark

History

Product Variants

Part Number	Color	Put-Up Type	Length
19230 010250	BLACK	Reel	250 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will, Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product listef or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.