

 **Part Number:** 37116

Hook-Up/Lead Wire UL AWM Style 3340 & 3374, (1) 16
AWG (26x30) TC, EPDM, 600V, 150°C

Product Description

One 16 AWG stranded (26x30) tinned copper conductor, EPDM insulation.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors
16	26x30	TC - Tinned Copper	1
Total Number of Conductors:			1

Insulation:

Material	Nominal Wall Thickness
EPDM - Ethylene Propylene Diene Monomer Rubber	0.045 in

Outerjacket 1:

Nominal Diameter
0.154 in

Electrical Characteristics

Voltage:

UL Voltage Rating
600 V RMS (UL AWM Style 3340)
600 V RMS (UL AWM Style 3374)

Use

Safety

Temperature Range

UL Temp Rating:	125°C (UL AWM Style 3340) 125°C (UL AWM Style 3374) 150 °C
-----------------	--

Mechanical Characteristics

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CSA Rating:	CSA Rating
CSA Type:	CSA Type
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
UL AWM Style:	UL AWM Style
UL Rating:	UL Rating
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

History

Product Variants

Part Number	Color	Put-Up Type	Length
37116 002500	RED	Reel	500 ft
37116 004500	YELLOW	Reel	500 ft
37116 005500	GREEN, DARK	Reel	500 ft
37116 009500	WHITE	Reel	500 ft
37116 0104000	BLACK	Reel	4000 ft
37116 0105000	BLACK	Reel	5000 ft
37116 010500	BLACK	Reel	500 ft
37116 013500	BLUE, DARK	Reel	500 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their

individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.