

#### SPECIALIZING IN LCD / LED MONITORS























# 32PVMV

## **OVERVIEW**

The ORION Images 32inch value PVM (Public View Monitor) with built in camera and motion detection sensor becomes a highly effective theft deterrent tool creating awareness that a security surveillance system is in place. The optional built in media card reader turns your loss prevention display into an advertising and marketing tool using pre loaded marketing material that can loop continuously.

## FEATURES

- Metal Chassis
- Duilt-In WDR 1/3" SONY 410K Double Scan CCD Camera / Tilt Swivel Camera
- 600 TV Line Horizontal Resolution
- 💿 0.4 / 0.0001 Lux
- LED Backlight Unit
- 1920 x 1080 Resolution, 400 Nits, 1300:1 Contrast
- 3D Comb Filter / De-Interlace
- PIR Motion Sensor (10 ~ 30 feet)
- BNC Video 1 In / 1 Out, Audio 1 In, HDMI 1 In, VGA 1 In, Camera 1 Out, PC Stereo 1 In
- Auto Source Sequencing









## **32PVMV**

#### **SPECIFICATIONS**

	32PVMV
Display	
Screen Size	32 Inch
Backlight Unit	LED BLU
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.36375 x 0.36375mm
Brightness	400cd/m <sup>2</sup>
Contrast Ratio	1300 : 1
Aspect Ratio	16:9
Viewing Angle (H/V)	178°/ 178°
Display Color	16.7 Million
Response Time	< 8ms
Video System	NTSC / PAL
Interface	
Video In / Out (BNC Type)	1 In / 2 Out (Include Camera Out)
HDMI In	1 ln
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	1 Left & Right
PC Stereo In	1 In
Transmitter	·
Remote Control	Yes
Audio	
Built-in Speakers	Yes (7.5W x 2)
Features	
Filter Type	3D Comb Filter / De-Interlacing
Auto Source Sequencing	Yes
Motion Detection	PIR Motion Sensor (10~30 feet)
LCD Protection Glass	No
Multi Language	English, Spanish, French, German, Italian
Camera	English, Opanish, French, German, Rahan
Camera Type	WDR Camera
Image Sensor	1/3" SONY 410K Double Scan CCD
Scanning System	2 : 1 interlace
Mechanical Design	Tilt Swivel Camera
S/N Ratio	>52 dB
Resolution	Horizontal : 600 TV Lines
Lens Mount Sensitivity Electronoc Shutter	2.8~12mm Vari-focal Lens(F=1.2)
	0.4 Lux with F1.2 Lens
	0.0001 Lux
	1/60 ~ 1/10,000 Sec
General	20.64" x 20.20" x 2.45"
Outline Dimension (W x H x D)	29.61" x 20.28" x 3.15"
Net Weight	21.0Kg (46.3 lbs)
Material	Electronic galvanized Iron
Color	Black (Optional White)
Part / Labor	3year / 3year
Consumption: < On	< 110W
	AC100 ~ 240V(50/60Hz)
Operating Temperature	0 ~ 40°C / 32 ~ 104°F
Storage Temperature	-20 ~ 60°C / -4 ~ 140°F
Mounts	
VESA <sup>™</sup> Mount Size	200 x 200mm
Wall	WB-2642
Ceiling	CMK-01

Camera Cover



Screwless magnetic camera cover lid

Input Cover




Screwless magnetic rear cover lid

#### **INPUT INTERFACE**



## DIMENSIONS



## **OPTIONAL MOUNTS**



#### **ADVANTAGES**

#### **Motion Detection**

A motion detector is a device that detects moving objects, particularly people. A motion detector is often integrated as a component of a system that automatically performs a task or alerts a user of motion in an area.





After detect any motion



7300 Bolsa Avenue, Westminster, CA 92683 Tel. 714.766.6300 / Fax. 714.766.6310 / sales@orionimages.com / www.orionimages.com

