

Part Number: 7938A

Cat 5e 10m Flex DataTuff®, (4 pr) 24 AWG (7x32) CA,
PO/TPE/TPE, Foil+TC Braid Shld, Weldsplatter Res

Product Description

Four Cat 5e 24 AWG stranded (7x32) bare copper alloy conductors, bonded pairs, polyolefin insulation, TPE inner jacket, Beldfoil® shield (100% coverage) plus tinned copper braid (85% coverage), Weld splatter-resistant TPE jacket.

Product Specifications

Technical Specifications

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, Robotic Applications, Flexible Applications, 100MHz Category 5e, Industrial Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, CMX - Outdoor, RJ-45 Compatible*
-------------------------------	--

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Pairs
24	7x32	CA - Copper Alloy	4

Total Number of Conductors:	8
------------------------------------	---

Insulation:

Material
PO - Polyolefin

Color Chart 1:

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Innerjacket:

Material	Nominal Diameter	Nominal Wall Thickness
TPE	0.254 in	0.02 in

Outershield 1:

Type	Material	Material Trade Name	Coverage [%]	Nominal Diameter
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	
Braid	TC - Tinned Copper		85 %	0.282 in

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
Industrial Grade TPE - Theroplastic Elastomer	0.342 in	0.03 in	No	Polyester
	0.342 in			

Electrical Characteristics

Conductor DCR:

Max. Conductor DCR	Max. DCR Unbalance
11 Ohm/1000ft	3 %

Capacitance:

Max. Capacitance Unbalance	Nom.Mutual Capacitance
330 pF/ft	15 pF/ft

Delay:

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
510 ns/100m	45 ns/100m	69 %	12 ns/ft

High Freq:

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.5 db/100m	65.3 dB	62.3 dB	62.8 dB	59.8 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm	
4 MHz	4.9 db/100m	56.3 dB	53.3 dB	51.4 dB	48.4 dB	51.7 dB	48.7 dB	23 dB	23 dB	100 ± 15 Ohm	
8 MHz	6.9 db/100m	51.8 dB	48.8 dB	44.9 dB	41.9 dB	45.7 dB	42.7 dB	24.5 dB	24.5 dB	100 ± 15 Ohm	
10 MHz	7.8 db/100m	50.3 dB	47.3 dB	42.5 dB	39.5 dB	43.8 dB	40.8 dB	25 dB	25 dB	100 ± 15 Ohm	
16 MHz	9.9 db/100m	47.3 dB	44.3 dB	37.4 dB	34.4 dB	39.7 dB	36.7 dB	25 dB	25 dB	100 ± 15 Ohm	
20 MHz	11.1 db/100m	45.8 dB	42.8 dB	34.7 dB	31.7 dB	37.7 dB	34.7 dB	25 dB	25 dB	100 ± 15 Ohm	
25 MHz	12.5 db/100m	44.3 dB	41.3 dB	21.8 dB	28.8 dB	35.8 dB	32.8 dB	24.3 dB	24.3 dB	100 ± 15 Ohm	
31.25 MHz	14.1 db/100m	42.9 dB	39.9 dB	28.8 dB	25.8 dB	33.9 dB	30.9 dB	23.6 dB	23.6 dB	100 ± 15 Ohm	
62.5 MHz	20.4 db/100m	38.4 dB	35.4 dB	18 dB	15 dB	27.8 dB	24.8 dB	21.5 dB	21.5 dB	100 ± 15 Ohm	
100 MHz	26.4 db/100m	35.3 dB	32.3 dB	8.9 dB	5.9 dB	23.8 dB	20.8 dB	20.1 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm
1 MHz											
4 MHz											
8 MHz											
10 MHz											
16 MHz											
20 MHz											
25 MHz											
31.25 MHz											
62.5 MHz											
100 MHz											

Voltage:

UL Voltage Rating

300 V RMS

Use

Suitability - Oil Resistance:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	40 lbs

Safety

C(UL) Flammability:	FT1
UL Flammability:	UL1581 Vertical Tray (VW-1)

Temperature Range

Installation Temp Range:	-25°C To +75 °C
Operating Temp Range:	-40°C To +80°C
Storage Temp Range:	-40°C To +80 °C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	3.5 in
-----------------------------	--------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

ISO/IEC Compliance:	Other Standards
CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
Other Specification:	Other Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

History

Notes:	Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. *Special RJ45 plugs required. See WWW.BELDEN.COM - Tools - Connector Cross Reference.
--------	--

Product Variants

Part Number	Color	Put-Up Type	Length
7938A B59500	BLACK, MATTE	Reel	500 ft

© 2016 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.