

USB 3.1 Gen 1 to VGA DisplayPort Alternate Mode Dual/Multi-Monitor External Video Graphics Card Adapter, 1080p

MODEL NUMBER: **U444-06N-VGA-AM**



Description

The U444-06N-VGA-AM USB 3.1 Gen 1 to VGA Alternate Mode Dual/Multi-Monitor External Video Graphics Card Adapter supports USB DisplayPort Alternate Mode for displaying video on a VGA monitor or projector via your computer, tablet, laptop or smartphone's USB-C™ port. It's an ideal tool for multitasking, viewing large spreadsheets, editing documents, giving presentations at trade shows and conferences, or playing games and watching movies on large screens.

You can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary display. No external power supply is needed. Connect the adapter's USB-C male plug to the USB-C port on your smartphone, tablet, Ultrabook or computer. Then, connect the adapter's VGA female port to a monitor using a VGA cable (such as Tripp Lite's P502-Series) to see and hear full DisplayPort audio and video.

The U444-06N-VGA-AM supports high-definition (HD) video resolutions up to 1920 x 1200 (@ 60 Hz), including 1080p, and data transfer rates up to 5 Gbps. It also supports 36-bit Deep Color (12 bits per channel). Compatible with USB-C devices that support USB DisplayPort Alternate Mode.

Features

Easy to Add a Display

- Supports USB DisplayPort Alternate Mode for transmitting video to a VGA display via your computer, tablet, laptop or smartphone's USB-C port
- Extend video to a second monitor, duplicate the same video on both monitors, or make the second monitor your primary display
- Ideal for multitasking, viewing spreadsheet data, editing documents, giving presentations, watching movies and playing video games
- No external power supply or drivers required
- Compatible with USB-C devices that support USB DisplayPort Alternate Mode

Vibrant, Superior Video Quality

- Supports high-definition video resolutions up to 1920 x 1200 (@ 60 Hz), including 1080p
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting video
- Extend video to a second display or duplicate one video on both
- Supports HD video resolutions up to 1080p (@ 60 Hz)
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- No external power supply or drivers required

System Requirements

- USB-C device that supports USB DisplayPort Alternate Mode
- VGA-enabled monitor

Package Includes

- U444-06N-VGA-AM USB 3.1 Gen 1 to VGA Alternate Mode Dual/Multi-Monitor External Video Graphics Card Adapter
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports 36-bit Deep Color (12 bits per channel)

Specifications

CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>