

CORNING

UniCam® High-Performance Installation Tool Kit 2

CORNING

Specifications

| General Specifications | |
|------------------------|-------------------------------|
| Product type | Connector tools and tool kits |
| Technology | No-epoxy/no-polish |
| Compatibility | LC, SC and ST® compatible |
| Product category | Core product |

| Mechanical Characteristics | |
|----------------------------|--|
| Weight | 3.54 kg (7.8 lb) |
| Dimensions (HxWxD) | 10.8 cm x 38.7 cm x 30.5 cm (4.25 in x 15.25 in x 12 in) |

| Chemical Characteristics | |
|--------------------------|---|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |

Ordering Information

| | |
|---------------------|---|
| Part Number | TKT-UNICAM-PFC2 |
| Product Description | UniCam® high-performance tool kit 2: includes high-performance installation tool 2 for termination of multimode and single-mode LC, SC and ST® compatible connectors; includes high-performance precision flat cleaver and all required fiber preparation, cleaning tools and materials |

Shipping Information

| | |
|--------------------|--|
| Units Per Delivery | 1/1 |
| Package Contents | UniCam® high-performance installation tool 2, precision flat fibre cleaver, crimp tool, 7-in LCD video panel, fibre preparation tools and fibre cleaning tools |
| Dimensions (HxWxD) | 17.8 cm x 48.3 cm x 35.6 cm (7 in x 19 in x 14 in) |
| Shipping Weight | 4.22 kg (9.3 lb) |

UniCam® High-Performance Installation Tool Kit 2

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Notes



**Corning Optical Communications GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY
00 800 2676 4641 · FAX: +49 30 5303 2335 · www.corning.com/opcomm/emea**

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2016 Corning Optical Communications. All rights reserved.