



Part Number: 9488

600V Tray Cable

Product Description

14 AWG pairs stranded (42x30) tinned copper conductors, twisted pairs, PVC/Nylon insulation, unshielded, PVC jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Pairs
14	42x30	TC - Tinned Copper	1
Total Number of Conductors:			2

Insulation:

Material
PVC/Nylon - Polyvinyl Chloride/Nylon

Color Chart 1:

Number	Color
1	Black & Red

Outersheild 1:

Material
Unshielded

Outerjacket 1:

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.359 mm	0.048 mm	Yes

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR
2.6 Ohm/km

Capacitance:

Nom. Capacitance Conductor to Conductor
50 pF/m

Current:

Max. Recommended Current [A]
25 Amps per conductor @ 25°C

Inductance:

Nominal Inductance
0.24 μ H/m

Voltage:

UL Voltage Rating
600V RMS (NEC Type TC)
150V RMS (NPLF)

Use

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	107 lbs

Safety

C(UL) Flammability:	FT4
IEEE Flammability:	1202
UL Flammability:	UL1685 UL Loading

Temperature Range

Dry Temp Range:	-30°C To +90 °C
Wet Temp Range:	-30°C To +90°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	3.75 in
-----------------------------	---------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
NEC/(UL) Specification:	NPLF^TC^THHN/THWN Singles
Other Specification:	ICEA S-73-532, S-61-402
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

History

Notes:	Alternate color coding available upon request.
--------	--

© 2016 Belden, Inc
All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.