



**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 1

Compilation date: 12/03/2014

Revision date: 02/02/2016

Revision No: 14

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** FLAWFINDER DYE PENETRANT SPRAY

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Dye penetrant.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Flam. Aerosol 1: H222; -: H229

**Most important adverse effects:** Extremely flammable aerosol. Pressurised container: May burst if heated.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

**Hazard pictograms:** GHS02: Flame



**Signal words:** Danger

**Precautionary statements:** P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Do not pierce or burn, even after use.

[cont...]

# SAFETY DATA SHEET

## FLAWFINDER DYE PENETRANT SPRAY

Page: 2

P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.

No smoking.

P211: Do not spray on an open flame or other ignition source.

P285: In case of inadequate ventilation wear respiratory protection.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

### 2.3. Other hazards

**Other hazards:** Danger of serious damage to health by prolonged exposure.

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### WHITE MINERAL OIL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
232-455-8	8042-47-5	Substance with a Community workplace exposure limit.	-	50-70%

##### HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	22.5-30%
-----------	------------	--	-------------------------------------	----------

##### ODOURLESS KEROSENE - REACH registered number(s): 01-2119456620-43-XXXX

926-141-6	64742-47-8	-	Asp. Tox. 1: H304; -: EUH066	2.4-22.5%
-----------	------------	---	------------------------------	-----------

##### ACETONE - REACH registered number(s): 01-2119471330-49-XXXX

200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	1-2.4%
-----------	---------	---	--	--------

##### 2-NAPHTALENOL, 1-[[4-(PHENYLAZO)PHENYL]AZO]-, AR-HEPTYL AR',AR"-ME DERIVS.

296-120-8	92257-31-3	-	Repr. 2: H361f	1-2.4%
-----------	------------	---	----------------	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes.

**Ingestion:** Wash out mouth with water.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. If conscious, ensure the casualty sits or lies down. If unconscious and breathing is OK, place in the recovery position. If unconscious, check for breathing and apply artificial respiration if necessary. If breathing becomes bubbly, have the casualty sit and provide oxygen if available. Transfer to hospital as soon as possible.

[cont...]

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 3

**4.2. Most important symptoms and effects, both acute and delayed**

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

**Delayed / immediate effects:** No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

**Immediate / special treatment:** Not applicable.

**Section 5: Fire-fighting measures**

**5.1. Extinguishing media**

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

**5.2. Special hazards arising from the substance or mixture**

**Exposure hazards:** In combustion emits toxic fumes.

**5.3. Advice for fire-fighters**

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

**Section 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

**6.2. Environmental precautions**

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

**6.3. Methods and material for containment and cleaning up**

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

**6.4. Reference to other sections**

**Reference to other sections:** Refer to section 8 of SDS.

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Avoid direct contact with the substance. Ensure there is exhaust ventilation of the area. Avoid the formation or spread of mists in the air.

[cont...]

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Hazardous ingredients:**

**WHITE MINERAL OIL**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5 mg/m3	10 mg/m3	-	-

**HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)**

UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-
----	-------------------	-------------------	---	---

**ODOURLESS KEROSENE**

UK	1200	-	-	-
----	------	---	---	---

**ACETONE**

UK	1210 mg/m3	3620 mg/m3	-	-
----	------------	------------	---	---

**DNEL/PNEC Values**

**Hazardous ingredients:**

**ACETONE**

Type	Exposure	Value	Population	Effect
DNEL	Dermal	186	Workers	Local
DNEL	Inhalation	2420	Workers	Local
DNEL	Oral	62	Consumers	Systemic
PNEC	Fresh water	10.6	-	-
PNEC	Marine water	1.06	-	-
PNEC	Soil (agricultural)	33.3	-	-
PNEC	-	-	-	-

**8.2. Exposure controls**

**Engineering measures:** The floor of the storage room must be impermeable to prevent the escape of liquids.

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Protective gloves. Nitrile gloves.

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 5

**Eye protection:** Safety glasses.  
**Skin protection:** Protective clothing.  
**Environmental:** No data available

**Section 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**State:** Aerosol  
**Colour:** Red  
**Odour:** Characteristic odour  
**Evaporation rate:** Slow  
**Oxidising:** Non-oxidising (by EC criteria)  
**Solubility in water:** Not miscible  
**Viscosity:** Non-viscous  
**Boiling point/range°C:** No data available.      **Melting point/range°C:** No data available.  
**Flammability limits %: lower:** No data available.      **upper:** No data available.  
**Flash point°C:** <-60      **Part.coeff. n-octanol/water:** No data available.  
**Autoflammability°C:** No data available.      **Vapour pressure:** No data available.  
**Relative density:** < 1      **pH:** No data available.  
**VOC g/l:** No data available.

**9.2. Other information**

**Other information:** No data available.

**Section 10: Stability and reactivity**

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

**10.4. Conditions to avoid**

**Conditions to avoid:** Heat.

**10.5. Incompatible materials**

**Materials to avoid:** Strong oxidising agents. Strong acids.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

[cont...]

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 6

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Hazardous ingredients:**

**ODOURLESS KEROSENE**

DERMAL	RBT	LD50	>5000	mg/kg
ORAL	RBT	LD50	>5000	mg/kg
VAPOURS	RAT	4H LC50	>5000	mg/l

**ACETONE**

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3	gm/kg
ORL	RAT	LD50	5800	mg/kg

**Toxicity values:** No data available.

**Symptoms / routes of exposure**

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

**Delayed / immediate effects:** No data available.

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**ODOURLESS KEROSENE**

ALGAE	72H IC50	20	mg/l
Daphnia magna	48H EC50	>250	mg/l
FISH	96H LC50	>1000	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	>1000	mg/l

**ACETONE**

BLUEGILL (Lepomis macrochirus)	LC50	8300	mg/l
--------------------------------	------	------	------

**12.2. Persistence and degradability**

**Persistence and degradability:** Not biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** Bioaccumulation potential.

[cont...]

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 7

**12.4. Mobility in soil**

**Mobility:** Readily absorbed into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** Toxic to aquatic organisms. Toxic to soil organisms.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Recovery operations:** No data available

**Waste code number:** 16 05 04

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**14.1. UN number**

**UN number:** UN1950

**14.2. UN proper shipping name**

**Shipping name:** AEROSOLS, FLAMMABLE

**14.3. Transport hazard class(es)**

**Transport class:** 2.1

**14.4. Packing group**

**14.5. Environmental hazards**

**Environmentally hazardous:** No

**Marine pollutant:** No

**14.6. Special precautions for user**

**Special precautions:** No special precautions.

**Tunnel code:** D

**Transport category:** 2

**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

**Transport in bulk:** No data available.

**Section 15: Regulatory information**

[cont...]

**SAFETY DATA SHEET**  
FLAWFINDER DYE PENETRANT SPRAY

Page: 8

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**Specific regulations:** Not applicable.

**15.2. Chemical Safety Assessment**

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H304: May be fatal if swallowed and enters airways.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H361f: Suspected of damaging fertility.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.