

## TWAS-71620 - Torque Wrench, Speed Head, 7/16", 20 in/lb - Data Sheet

Torque Wrench Speed Head is designed to act like a ratcheting wrench. The tool skips over the corners of the bolt or nut being turned so no repositioning of the tool is required (allowing continuous turning).

Designed for "F" Connectors, these wrenches help prevent over tightening. An audible click tells you the connection has been properly achieved. These wrenches all have angle heads, sized for 7/16" F connectors and are designed with an ergonomic cushioned handle for user comfort and protection. These wrenches work in tightening mode only. Torque wrenches are configured for 20 in./lb. (2.26 in Newton Meters) covering most manufacturers' recommended torque requirements for their F connectors. Torque wrench is 6 1/2" long.



### Specifications

Head Type	Speed
Torque	20 inch-lbs (2.26 NM)
Size	7/16"
Head Angle	15 Degrees
Indicator	Audible Click
Length	6-1/2" (165.1mm)
Material	High Carbon Alloy Steel
Finish	Black Oxide
Handle	Ergonomic Cushion Grip
Color	Yellow Handle
Weight	0.404 lbs
UPC No.	811490010659