







## Stinger® RECHARGEABLE FLASHLIGHT

FL 1 STANDARD	
	<b>90 LUMENS</b>
	<b>1h 15min</b>
	<b>210m</b>
	<b>11,000cd</b>
	
	<b>2m</b>

Product is tested per ANSI/NEMA FL-1 2009 standard



Case Material: Machined aluminum housing that is anodized against corrosion inside and out and an unbreakable polycarbonate lens with scratch-resistant coating

Dimensions/ Length: 7.38 in. (18.7 cm)      Major Diameter: 1.60 in. (4.06 cm);      Body Diameter: 1.08 in. (2.74 cm)  
Weight: 10 ounces (284 grams)\*

Light Source: Xenon gas-filled bi-pin bulb with 30-hour life, with a spare stored in the end cap, variable spot-to-flood beam

On/Off: Push-button head switch. Momentary or constant on


Battery: 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times


Charging: Ten hours to fully recharge, 2.5-hour fast charger or PiggyBack® charger model available

Features:

- IPX4 rated design; water resistant
- LED charge-continuity indicator, compact
- Serialized for positive identification
- 2 meter impact resistance tested.
- Snap-in charger holder that mounts in any position

Approvals\*\*:

 UL Listed Class I, Div. 2, Groups A,B,C,D T1; Class II, Div. 2, Groups F,G T3

 Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited life-time warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Item
Stinger with 230V AC/DC	080926-75214-6	75214
Stinger with 120V AC/DC	080926-75014-2	75014
Stinger with 230V AC	080926-75201-6	75201
Stinger with 120V AC	080926-75001-2	75001
Stinger with 120V AC/DC	080926-75300-6	75300
Stinger	080926-75000-5	75000
See reverse for additional part numbers		



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
5 Unit Bank Charger, 100V	080926-75700-4	75700
5 unit bank charger 100V	080926-75701-1	75701
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
PiggyBack® Charger Holder Fast Charge & Battery	080926-75276-4	75276
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
Battery Stick (Lithium Ion)	080926-75176-7	75176

Item	UPC	Part #
Lens replacement kit	080926-75160-6	75160
Lens/Reflector Assembly	080926-75956-5	75956
Switch Module		
** Special tool required for installation	080926-75140-8	75140
Bulb	080926-75914-5	75914
Flip Lens IR	080926-75027-2	75027
Flip Lens Red	080926-75115-6	75115
Flip Lens Blue	080926-75116-3	75116
Flip Lens Green	080926-75117-0	75117
Safety Wand Blue	080926-75902-2	75902
Safety Wand Red	080926-75903-9	75903
Safety Wand Yellow	080926-75904-6	75904
Safety Wand White	080926-75908-4	75908
Safety Wand Glow in the Dark	080926-75913-8	75913
HP Upgrade Kit (Converts Stinger to Stinger HP)	080926-78004-0	78004
Holster, Stinger, Stinger XT, PolyStinger (Deluxe Nylon)	080926-75909-1	75909
Ring Holder	080926-75906-0	75906
Holster (Nylon)	080926-76090-5	76090
Loop holster	080926-75928-8	75928



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax  
 www.streamlight.com ©Streamlight, Inc. Stinger 8/15