Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

8761MN Multi-Conductor - SpaceMaker Audio, Control and Instrumentation Cable



For more Information please call

1-800-Belden1



General Description:

22 AWG stranded (19x34) TC conductors, polypropylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 24 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall) Conductor			
AWG:			
# PairsAWGStrandingConductor Material12219x34TC - Tinned Copper			
Total Number of Conductors:	2		
Insulation			
Insulation Material:			
Insulation Material Wall Thickness (in.) PP - Polypropylene 0.010			
Outer Shield Outer Shield Material:			
	Coverage (%)		
Beldfoil® Tape Aluminum Foil-Polyester Tape 1	00.000		
Outer Shield Drain Wire AWG:			
AWG Stranding Drain Wire Conductor Material 24 19x36 TC - Tinned Copper			
Outer Jacket Outer Jacket Material:			
Outer Jacket Material Nom. Wall Thickness (in.)			
PVC - Polyvinyl Chloride 0.016			
Overall Cable			
Overall Nominal Diameter:	0.135 in.		
Pair Pair Color Code Chart: Number Color 1 Black & White			
Mechanical Characteristics (Overall)			
Operating Temperature Range:	-20°C To +80°C		
Bulk Cable Weight:	11 lbs/1000 ft.		
Max. Recommended Pulling Tension:	27 lbs.		
Min. Bend Radius/Minor Axis:	0.540 in.		
Min. Bend Radius (Continuous Flexing):	1.350 in.		
Flex Cycle Rating:	1 Million Flexes		
Applicable Specifications and Agency Compliance (Overall)		
Applicable Standards & Environmental Programs			
NEC Articles:	800		
EU Directive 2011/65/EU (ROHS II):	Yes		
EU CE Mark:	Yes		
EU Directive 2000/53/EC (ELV):	Yes		
EU Directive 2002/95/EC (RoHS):	Yes		

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

8761MN Multi-Conductor - SpaceMaker Audio, Control and Instrumentation Cable

	EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004						
	EU Directive 2002/96/EC (WEEE):	Yes						
	EU Directive 2003/11/EC (BFR):	Yes Yes						
	CA Prop 65 (CJ for Wire & Cable):							
	MII Order #39 (China RoHS):							
	Other Specification:	UL Style AWM 2937 (300V 80C), NFPA 79						
Flame Test								
	CSA Flame Test:	FT1						
Sui	tability							
	Suitability - Indoor:	Yes						
Elec	ctrical Characteristics (Overall)							
	n. Characteristic Impedance:							
	mpedance (Ohm)							
	51.000							
Non	n. Inductance:							
	nductance (µH/ft)							
	0.031							
Non	n. Capacitance Conductor to Shield:							
	Capacitance (pF/ft)							
Ę	55.900							
Non	n. Capacitance Conductor to Conductor:							
	Capacitance (pF/ft)							
2	28.800							
Non	n. Conductor DC Resistance:							
I	DCR @ 20°C (Ohm/1000 ft)							
ľ	14.900							
Max	. Operating Voltage - UL:							
	Voltage 300 V RMS (UL AWM Style 2092)							
Max	. Recommended Current:							
	Current 2.9 Amps per conductor @ 25°C ambient							

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc	
8761MN 004100	100 FT	2.600 LB	YELLOW		1 PR #22 PO FS PVC	
8761MN 0041000	1,000 FT	12.000 LB	YELLOW		1 PR #22 PO FS PVC	
8761MN 006100	100 FT	2.600 LB	BLUE, LIGHT		1 PR #22 PO FS PVC	
8761MN 0061000	1,000 FT	12.000 LB	BLUE, LIGHT		1 PR #22 PO FS PVC	
8761MN 008100	100 FT	2.600 LB	GRAY		1 PR #22 PO FS PVC	
8761MN 0081000	1,000 FT	12.000 LB	GRAY		1 PR #22 PO FS PVC	

Revision Date: 09-22-2016 Revision Number: 0

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU ROHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is designed only as general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

^{© 2016} Belden, Inc All Rights Reserved