



SAFETY DATA SHEET

Janitol Original

According to Regulation (EC) No 1907/2006, Annex II, as amended by Regulation (EU) No 453/2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Janitol Original
Product number JAN60O,JAN76V,JAN84U

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Detergent.

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

Emergency telephone National Poisons Information Service (UK) 0344 8920111 (Health Professionals only)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification

Physical hazards Not Classified
Health hazards Skin Irrit. 2 - H315 Eye Dam. 1 - H318
Environmental hazards Not Classified

Classification (67/548/EEC or 1999/45/EC) Xi;R36.

Environmental The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

2.2. Label elements

Pictogram



Signal word Danger

Janitol Original

Hazard statements	H315 Causes skin irritation. H318 Causes serious eye damage.
Precautionary statements	P280 Wear protective gloves/protective clothing/eye protection/face protection. P302+P352 IF ON SKIN: Wash with plenty of water. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P313 Get medical advice/attention. P332+P313 If skin irritation occurs: Get medical advice/attention. P501 Dispose of contents/container in accordance with local regulations.
Contains	BENZENE SULPHONIC ACID , C10-13-ALKYL DERIVS., SODIUM SALTS, ISOTRIDEKANOL, ETHOXYLATED 6.5 MOL EO
Detergent labelling	5 - < 15% phosphates, < 5% anionic surfactants, < 5% non-ionic surfactants
Supplementary precautionary statements	P264 Wash contaminated skin thoroughly after handling. P362+P364 Take off contaminated clothing and wash it before reuse.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

TETRAPOTASSIUM PYROPHOSPHATE			5-10%
CAS number: 7320-34-5	EC number: 230-785-7	REACH registration number: 01-2119489369-18-xxxx	
Classification	Classification (67/548/EEC or 1999/45/EC)		
Eye Irrit. 2 - H319	Xi;R36.		
BENZENE SULPHONIC ACID , C10-13-ALKYL DERIVS., SODIUM SALTS			1-5%
CAS number: 68411-30-3	EC number: 270-115-0		
Classification	Classification (67/548/EEC or 1999/45/EC)		
Acute Tox. 4 - H302	Xn;R22. Xi;R38,R41.		
Skin Irrit. 2 - H315			
Eye Dam. 1 - H318			
Aquatic Chronic 3 - H412			
ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO			1-5%
CAS number: 69011-36-5	EC number: 931-138-8	REACH registration number: 01-2119976362-32-XXXX	
Classification	Classification (67/548/EEC or 1999/45/EC)		
Skin Irrit. 2 - H315	Xn;R22. Xi;R41.		
Eye Dam. 1 - H318			
Aquatic Chronic 3 - H412			

Janitol Original

ARYL ETHER PHOSPHATE ESTER, POTASSIUM SALT		1-5%
CAS number: 72283-31-9		
Classification	Classification (67/548/EEC or 1999/45/EC)	
Skin Irrit. 2 - H315	Xi;R36/38.	
Eye Irrit. 2 - H319		

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Not relevant. Unlikely route of exposure as the product does not contain volatile substances.
Ingestion	Rinse mouth thoroughly with water. Get medical attention if any discomfort continues.
Skin contact	Not applicable.
Eye contact	Remove any contact lenses and open eyelids wide apart. Important! Immediately rinse with water for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	No specific symptoms known.
Ingestion	No specific symptoms known.
Eye contact	Irritation of eyes and mucous membranes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations.
-----------------------------	------------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.
-------------------------------------	-----------------------------------------------------------------------------------------------

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products	No known hazardous decomposition products.
--------------------------------------	--------------------------------------------

5.3. Advice for firefighters

Protective actions during firefighting	No specific firefighting precautions known.
-----------------------------------------------	---------------------------------------------

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Wear protective clothing as described in Section 8 of this safety data sheet. Avoid contact with eyes.
-----------------------------	--------------------------------------------------------------------------------------------------------

6.2. Environmental precautions

Environmental precautions	Not considered to be a significant hazard due to the small quantities used.
----------------------------------	-----------------------------------------------------------------------------

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	Flush away spillage with plenty of water. Avoid contamination of ponds or watercourses with washing down water. Absorb spillage with non-combustible, absorbent material. Do not discharge into drains or watercourses or onto the ground.
--------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Janitol Original

6.4. Reference to other sections

Reference to other sections For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid contact with eyes.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in closed original container at temperatures between 0°C and 30°C.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Ingredient comments None.

TETRAPOTASSIUM PYROPHOSPHATE (CAS: 7320-34-5)

DNEL Professional - Inhalation; Long term systemic effects: 44.08 mg/m³
Consumer - Inhalation; Long term systemic effects: 10.87 mg/m³

PNEC - Marine water; 0.005 mg/l
- Fresh water; 0.5 mg/l
- STP; 50 mg/l
- Fresh water; 0.05 mg/l

BENZENE SULPHONIC ACID , C10-13-ALKYL DERIVS., SODIUM SALTS (CAS: 68411-30-3)

DNEL Workers - Inhalation; Long term systemic effects: 12 mg/m³
Workers - Inhalation; Long term local effects: 12 mg/m³
Workers - Dermal; Long term systemic effects: 170 mg/kg/day
General population - Inhalation; Long term systemic effects: 3 mg/m³
General population - Inhalation; Long term local effects: 3 mg/m³
General population - Oral; Long term systemic effects: 0.85 mg/kg/day

PNEC - Fresh water; 0.268 mg/l
- Marine water; 0.0268 mg/l
- Intermittent release; 0.0167 mg/l
- STP; 3.43 mg/l
- Sediment (Freshwater); 8.1 mg/kg
- Marine water; 8.1 mg/kg
- Soil; 35 mg/kg

ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO (CAS: 69011-36-5)

DNEL Workers - Inhalation; Long term systemic effects: 294 mg/m³
Workers - Dermal; Long term systemic effects: 2080 mg/kg
General population - Inhalation; Long term systemic effects: 87 mg/m³
General population - Dermal; Long term systemic effects: 1250 mg/kg/day
General population - Oral; Long term systemic effects: 25 mg/kg/day

Janitol Original

PNEC

- Fresh water; 0.074 mg/l
- Marine water; 0.0074 mg/l
- Intermittent release; 0.015 mg/l
- STP; 1.4 mg/l
- Sediment (Freshwater); 0.604 mg/kg
- Sediment (Marinewater); 0.0604 mg/kg
- Soil; 0.1 mg/kg

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Not relevant.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material.

Hygiene measures

Wash hands after contact.

Respiratory protection

Not relevant.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Yellow.
Odour	Characteristic.
Odour threshold	Not determined. Not determined.
pH	pH (concentrated solution): 10-10.5
Melting point	Not determined.
Initial boiling point and range	Not determined.
Flash point	Not determined.
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Scientifically unjustified. : : Scientifically unjustified.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	1.06-1.1 @ 25°C
Solubility(ies)	Soluble in water.
Auto-ignition temperature	Scientifically unjustified.
Decomposition Temperature	Not determined.

Janitol Original

Viscosity	Not determined.
Explosive properties	Scientifically unjustified.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information	No information required.
-------------------	--------------------------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
------------	---------------------------------------------------------------------

10.2. Chemical stability

Stability	Stable at normal ambient temperatures.
-----------	----------------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not known.
------------------------------------	------------

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
---------------------	-----------------------------------------------------------------------------------

10.5. Incompatible materials

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
--------------------	------------------------------------------------------------------------------------------------------------------

10.6. Hazardous decomposition products

Hazardous decomposition products	No known hazardous decomposition products.
----------------------------------	--------------------------------------------

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

ATE oral (mg/kg)	34,181.54196734
------------------	-----------------

Acute toxicity - dermal

Notes (dermal LD ₅₀)	Based on available data the classification criteria are not met.
----------------------------------	------------------------------------------------------------------

Skin corrosion/irritation

Animal data	Moderately irritating.
-------------	------------------------

Serious eye damage/irritation

Serious eye damage/irritation	Based on available data the classification criteria are not met.
-------------------------------	------------------------------------------------------------------

Skin sensitisation

Skin sensitisation	Based on available data the classification criteria are not met.
--------------------	------------------------------------------------------------------

Germ cell mutagenicity

Genotoxicity - in vivo	Does not contain any substances known to be mutagenic.
------------------------	--------------------------------------------------------

Carcinogenicity

Carcinogenicity	Does not contain any substances known to be carcinogenic.
-----------------	-----------------------------------------------------------

Reproductive toxicity

Janitol Original

Reproductive toxicity - development Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure No information available.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure No information available.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

Inhalation No specific health hazards known.

Ingestion May cause discomfort if swallowed.

Skin contact Skin irritation should not occur when used as recommended.

Eye contact Irritating to eyes.

SECTION 12: Ecological Information

Ecotoxicity Not regarded as dangerous for the environment.

12.1. Toxicity

Toxicity The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

12.2. Persistence and degradability

Persistence and degradability The surfactant(s) contained in this product complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them at their direct request, or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

12.4. Mobility in soil

Mobility The product is soluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information When handling waste, the safety precautions applying to handling of the product should be considered.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. No specific disposal method required. Reuse or recycle products wherever possible.

Janitol Original

SECTION 14: Transport information

Road transport notes Not classified.

Rail transport notes Not classified.

Sea transport notes Not classified.

Air transport notes Not classified.

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Not applicable.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78

and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Key literature references and sources for data

Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet.

Revision comments

SDS amended in line with REGULATION (EC) No 1272/2008 on Classification, Labelling and Packaging of Substances and Mixtures (as amended)

Revision date

26/04/2016

Janitol Original

Revision	2
Supersedes date	13/05/2015
Risk phrases in full	R22 Harmful if swallowed. R36 Irritating to eyes. R36/38 Irritating to eyes and skin. R38 Irritating to skin. R41 Risk of serious damage to eyes.
Hazard statements in full	H302 Harmful if swallowed. H315 Causes skin irritation. H318 Causes serious eye damage. H319 Causes serious eye irritation. H412 Harmful to aquatic life with long lasting effects. H302 Harmful if swallowed. H315 Causes skin irritation. H318 Causes serious eye damage. H319 Causes serious eye irritation. H412 Harmful to aquatic life with long lasting effects.
Notes for Risk Phrases and Hazard Statements in Full	The full text for Risk Phrases and Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.