



CCRRD | IP6A-12LUTP-1100E-1100E

**InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 12 links**

## Ordering Details

Complete Part Number	Complete Description Code	Interface Orientation, connector A	Interface Orientation, connector B	Bundling Style	Information Outlet Color	Cable Jacket Color	Length
CCRRD-53SA08F020	IP6A-12LUTP-1100E-1100E-LSF-RSF-SG-WH-20F	5 - Left series flat	3 - Right series flat	S - Sleeving	0 - Not applicable	8 - White	20 ft

↳ InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 12 links, left series flat to right series flat, sleeving, white jacket, 20 ft

## Dimensions

Cord Length, minimum	5 m   17 ft
Cord Length, maximum	90 m   295 ft

## Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

## General Specifications

Brand	GigaSPEED X10D®   InstaPATCH® Cu   SYSTIMAX®
Cable Type	U/UTP (unshielded)
Interface, connector A	360 1100 Evolve module
Interface, connector B	360 1100 Evolve module
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

## Mechanical Specifications

Link Count	12
Conductor Type	Solid

CCRRD | IP6A-12LUTP-1100E-1100E

Wiring T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

- 760151183 | 360-IPR-1100-GS6-DM6 — SYSTIMAX 360™ GigaSPEED X10D® 1100GS6 Evolve Category 6A U/UTP Distribution Module, 6 port
- 3091B 4/23 (Product Component—not orderable) — GigaSPEED X10D® 3091B ETL Verified Category 6A U/UTP Cable, 4 pair count,