



CJSXD | IP06-12LUTP-1LK12-BLUNT

InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Preterminated Copper Cable, dual row OneLink 2x6 to unterminated, 12 links

Ordering Details

Complete Part Number	Complete Description Code	Interface Orientation, connector A	Interface Orientation, connector B	Bundling Style	Information Outlet Color	Cable Jacket Color	Length
----------------------	---------------------------	------------------------------------	------------------------------------	----------------	--------------------------	--------------------	--------

CJSXD-6XHA08F045	IP06-12LUTP-1LK12-BLUNT-TPF-HG-WH-45F	6 - Trident paired flat	X - Not applicable	H - Hook-n-loop	0 - Not applicable	8 - White	45 ft
------------------	---------------------------------------	-------------------------	--------------------	-----------------	--------------------	-----------	-------

↳ InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Preterminated Copper Cable, dual row OneLink 2x6 to unterminated, 12 links, trident paired flat to not applicable, hook-n-loop, white jacket, 45 ft

Dimensions

Cord Length, minimum	2 m 7 ft
Cord Length, maximum	30 m 98 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Brand	GigaSPEED XL® InstaPATCH® Cu SYSTIMAX®
Cable Type	U/UTP (unshielded)
Interface, connector A	OneLink 2x6
Interface, connector B	Unterminated
Interface Feature, connector A	Standard

Mechanical Specifications

Link Count	12
Conductor Type	Solid
Wiring	T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

3071E 4/23 (Product Component—not orderable) — GigaSPEED XL® 3071 ETL Verified Category 6 U/UTP Cable, low smoke zero halogen, 4 pair count