

Part Number: 29528C

600V VFD, (3) 1 AWG (19x14) BC+Grd, XLPE/PVC, Foil Shld, TC-ER



Product Description

Three 1 AWG stranded (19x14) bare copper circuit conductors plus three symmetrical ground wires, cross-linked polyethylene insulation, two spiral copper tape shields (100% Coverage), PVC jacket.

Product Specifications

Technical Specifications

Suitable Applications:	AC Motor drives, VFD, Variable Frequency drives
-------------------------------	---

Construction and Dimensions

Conductor:

Element	AWG	Stranding	Material	No. of Conductors
	1	19x14	BC - Bare Copper	3
Ground Wire	10	7x18	BC - Bare Copper	

Total Number of Conductors:	3
------------------------------------	---

Insulation:

Material	Nominal Wall Thickness
XLPE - Cross Linked Polyethylene	0.057 in

Stranding:

Lay Length
Y mm

Outersheild 1:

Type	Layer	Material	Coverage [%]
Tape	1	Spiral Copper	100 %
Tape	2	Spiral Copper	100 %

Outerjacket 1:

Material	Nominal Diameter
PVC - Polyvinyl Chloride	1.121 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR
0.13 Ohm/1000ft

Capacitance:

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
44 pF/ft	79 pF/ft

Current:

Max. Recommended Current [A]
150 Amps per conductor @ 30°C (per NEC)

Inductance:

Nominal Inductance
0.146 μ H/ft

Voltage:

Description	UL Voltage Rating	Voltage Rating [V]
CSA AWM I/II A/B	600 V RMS (NEC Type TC)	1000 V RMS

Use

Suitability - Oil Resistance:	Yes
Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
Max Recommended Pulling Tension:	2650 lbs

Safety

CSA Flammability:	FT4
IEEE Flammability:	1202
UL Flammability:	UL1685 UL Loading

Temperature Range

Operating Temp Range:	-40°C To +90°C
UL Temp Rating:	90°C Wet/Dry

Mechanical Characteristics

Min Bend Radius/Minor Axis:	11.2 in
-----------------------------	---------

Part Number

Plenum (Y/N):	No
---------------	----

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
CSA AWM Specification:	CSA Specification
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC Articles:	NEC Articles
NEC/(UL) Specification:	NEC/(UL) Specification
PMSHA Specification:	PMSHA Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Product Variants

Part Number	Color	Put-Up Type	Length
29528C 0101000	BLACK	Reel	1000 ft
29528C 0103000	BLACK	Reel	3000 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its

publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.