



Part Number: 3093A

ControlNet™, (1) 18 AWG Solid BCCS, FFEP/PVDF, Foil+Braid Shld, CMP

Product Description

One 18 AWG solid bare copper-covered steel conductor, foam fluorinated ethylene propylene (FFEP) insulation, Duobond® IV Quad Shield (100% coverage), fluorocopolymer (PVDF) Jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.04 in	1
Total Nu	umber of Conduc	tors: 1		

Insulation:

Material	Nominal Diameter
FFEP - Foam Fluorinated Ethylene Propylene	0.17 in

Outershield 1:

Туре	Layer	Material	Material Trade Name	Coverage [%]
Таре	1	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	Bonded Duofoil®	100 %
Braid	2	AL - Aluminum		60 %
Таре	3	Aluminum Foil-Polyester Tape-Aluminum Foil	Duofoil®	100 %
Braid	4	AL - Aluminum		40 %

Outerjacket 1:

Material	Nominal Diameter
PVDF - Fluorocopolymer	0.274 in

Electrical Characteristics

Conductor DCR:

Nominal Conductor DCR	Nominal Outer Shield DCR
28 Ohm/1000ft	3.6 Ohm/1000ft

Capacitance:

Nom. Capacitance Conductor to Shield	
16.3 pF/ft	

Impedance:

Nominal Characte	istic Impedance
75 Ohm	

High Frequency (Nominal/Typical):

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.36 db/100ft
2 MHz	0.38 db/100ft
5 MHz	0.5 db/100ft
10 MHz	0.65 db/100ft
20 MHz	0.95 db/100ft
50 MHz	1.5 db/100ft
100 MHz	2.12 db/100ft
200 MHz	2.99 db/100ft
300 MHz	3.66 db/100ft
400 MHz	4.23 db/100ft

Delay:

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.28 ns/ft	82 %

High Freq:

Frequency [MHz]	Min. SRL (Structural Return Loss)
1 MHz	23 dB
2 MHz	
5 MHz	
10 MHz	
20 MHz	
50 MHz	
100 MHz	
200 MHz	
300 MHz	
400 MHz	
5 MHz	
50 MHz	

Inductance:

Nominal Inductance	
0.093 µH/ft	

Use

Suitability - Burial:	Yes
Suitability - Outdoor:	Yes
Max Recommended Pulling Tension:	104 lbs

<u>Safety</u>

UL Flammability:	NFPA 262

Temperature Range

Non-UL Temp Rating:	150°C
Operating Temp Range:	-20°C To +150°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	2.75 in

Part Number

Plenum (Y/N):	Yes
Non-Plenum Number:	3092A

Standards

CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)	
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)	
NEC/(UL) Specification:	NEC/(UL) Specification	
RG Type:	RG Type	
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)	

History

Notes:	Blue available as standard in 1000-ft put-up only. Suitable for Outdoor and Direct Burial applications.

Product Variants

Part Number	Color	Put-Up Type	Length
3093A 0101000	BLACK	Reel	1000 ft
3093A 0102000	BLACK	Reel	2000 ft
3093A 0102500	BLACK	Reel	2500 ft
3093A 0105000	BLACK	Reel	5000 ft
3093A X7E1000	BLUE X7E	Reel	1000 ft

© 2016 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor?s inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden?s knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product tiself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Part # PF_3093A | Page 4 of 4 | July 08, 2016

Belden Inc. | belden.catalog.belden.com/en/Products/Detail/PF_3093A