


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG TO INDICATE PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PRODUCT DESCRIPTION:
 - A. 1 LANE, 10 Gbps/LANE
 - B. STANDARD SFP+ CONNECTOR
 - C. CL2 RATED JACKET
 - D. JACKET COLOR: BLUE (BU), WHITE (WH), OR BLACK (BL)
4. MATES WITH SFP+ SFF-8431 INTERFACE
5. CABLE LABEL CONTAINS PRODUCT DESCRIPTION, PART NUMBER, LENGTH AND WIRE GAUGE, AND MANUFACTURING SERIAL NUMBER.

TABLE 1
CABLE ASSEMBLY

PART NUMBER	LENGTH METERS (+.15, -0)	LENGTH FEET (+.5, -0)	CABLE AWG	WEIGHT LBS
PSF1AXA3M**	3	9.84	30	0.24
PSF1AXA5M**	5	16.40	30	0.35
PSF1AXD7M**	7	22.97	24	0.81
PSF1AXD8M**	8	26.24	24	0.91
PSF1AXD9M**	9	29.52	24	1.01
PSF1AXD10M**	10	32.80	24	1.11

**CABLE COLOR IN BLUE (BU), WHITE (WH), BLACK (BL), RED (RD), GREEN (GR), OR ORANGE (OR)

PART NUMBER	SEE TABLE 1	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A

TITLE

ACTIVE SFP+ 10Gb/s CABLE ASSEMBLY

CUSTOMER DRAWING


ITEM REVISION NAME		10M187BQ/00.PRT		PANDUITTM	
DATASET FILE NAME		10M187BQ_DC15/00E.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL :	
.X ± 					

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	9-30-15	BJN	SCAL	DFP	H. REMVD 11M-15M LENGTH TO BE CONSISTENT W/CONTROL DWG G. ADDED RED, GREEN & ORANGE CABLE COLORS REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	10M187BQ-15

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW
SEE TABLE 2

TABLE 2
PINOUT DIAGRAM

BOTTOM SIDE		TOP SIDE	
POS #	SIGNAL	POS #	SIGNAL
1	VEET*	11	VEER*
2	TX_FAULT	12	RD-
3	TX_DISABLE	13	RD+
4	SDA	14	VEER*
5	SCL	15	VCCR
6	MOD_ABS	16	VCCT
7	RS0	17	VEET*
8	RX_LOS	18	TD+
9	RS1	19	TD-
10	VEER*	20	VEET*

* VEE PINS CONNECT FIRST
UPON PLUGGING IN.

PART NUMBER SEE TABLE 1		PRODUCT SPEC/PKG SPEC N/A	
I.T. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE ACTIVE SFP+ 10Gb/s CABLE ASSEMBLY CUSTOMER DRAWING			
ITEM REVISION NAME 10M187BQ/00.PRT			
DATASET FILE NAME 10M187BQ_DC15/00E.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .XXX ± ANGLES ±		MATERIAL:	
 THIRD ANGLE PROJECTION		DRAWING NUMBER: 10M187BQ-15	
DRAWN BY BJN	DATE 11-8-10	CHK WFM	SCALE NONE
SHT 2 OF 2		SIZE A	