



Part Number: 83932

Thermocouple Extension, (2) 20 AWG (7x28) Type KX,
FEP/FEP, PLTC, High-Temp

Product Description

Two 20 AWG stranded (7x28) Type KX conductors, fluorinated ethylene propylene (FEP) insulation, fluorinated ethylene propylene (FEP) jacket.

Product Specifications

Technical Specifications

Construction and Dimensions

Conductor:

AWG	Stranding	Material	No. of Conductors
20	Solid	Chromel	1
20	Solid	Alumel	1
Total Number of Conductors:			2

Insulation:

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.01 in

Outershield 1:

Material
Unshielded

Outerjacket 1:

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	0.076 x 0.128 in

Print Legend:	BELDEN 83932 E34972 2C20 (UL) CL3P 200C PLTC SUN RES THCPL EXTN KX (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
---------------	--

Electrical Characteristics

Conductor DCR:

Element	Nominal Conductor DCR
CHROMEL	420 Ohm/1000ft
ALUMEL	169 Ohm/1000ft

Use

Safety

UL Flammability:	UL910 Steiner Tunnel
------------------	----------------------

Temperature Range

Non-UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Min Bend Radius/Minor Axis:	1.25 in
-----------------------------	---------

Part Number

Plenum (Y/N):	Yes
---------------	-----

Standards

ANSI Compliance:	ANSI Specification
CA Prop 65 (CJ for Wire & Cable):	CA Prop 65 (CJ for Wire & Cable)
MII Order #39 (China RoHS):	MII Order #39 (China RoHS)
NEC/(UL) Specification:	NEC/(UL) Specification
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	EU CE Mark

History

Notes:	Chromel & Alumel = "Chromel and Alumel are Hoskins Manufacturing Company trademarks."
--------	---

Product Variants

Part Number	Color	Put-Up Type	Length
83932 0041000	YELLOW	Reel	1000 ft

© 2016 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.