


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES. UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-100A

TOOL WEIGHT: 7.2 oz. (205 g)

WIRE CUTTER for NO. 10 AWG and smaller copper wire.

CRIMPING DIES for Pan-Term insulated terminals, disconnects, splices and wire joints on No. 22 to 10 AWG stranded wire.

CUTTERS for machine screws of sizes shown.

CRIMPING DIE for Pan-Term non-insulated terminals, disconnects, splices and wire joints on No. 22 to 10 AWG solid or stranded wire.

CRIMP POCKETS A and B for additional terminals and disconnects per instructions on product packaging.

WIRE STRIPPER for removing plastic or rubber wire insulation. Strip length should allow a minimum of 1/32" of conductor to extend beyond terminal barrel.

DIMENSIONS IN PARENTHESES ARE (mm).

										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										CT-100A Crimping Tool			
										Customer Drawing			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN MILLIMETERS, THIRD ANGLE PROJECTION.	
										DRAWN BY: BLR		SCALE: NONE	
										DATE: 2-26-15		DRAWING NO. TP27597C01	
										CHK'D: [Signature]		DWG SIZE: C	
00	2-26-15	BLR	[Signature]	RELEASED	4857	---							
REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP					