

# FREEDM® One Tight-Buffered, Interlocking Armored Cable, Plenum

24 F, Single-mode (OS2)

CORNING

Corning FREEDM® One interlocking armored cables are flame-retardant, indoor/outdoor cables designed for interbuilding and intrabuilding backbone installations that eliminate the need for a transition splice when entering the building. Encased in a spirally wrapped, aluminum interlocking armor for ruggedness and superior crush resistance, these cables are ideal for industrial and heavy traffic areas and installations requiring extra protection for optical cables. These cables are protected against water penetration by innovative waterblocking technology, making them ideal for OSP applications. The flexible, interlocking armored design offers up to seven times the crush protection compared to unarmored cables (as characterized to ICEA-696) and allows easy one-step installation, thereby reducing overall installation costs. The UV-resistant, flame-retardant jacket is rugged, durable and easy to strip.

*Note: This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.*

## Features and Benefits

### Waterblocking technology

OSP (outdoor) applications

### Flexible, interlocking armor design

Seven times crush protection compared to unarmored cables

### UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



## Standards

### Approvals and Listings

National Electrical Code® (NEC®) OFCP, CSA FT-4, ICEA S-104-696

### Flame Resistance

NFPA 262 (for plenum, riser and general building applications)



# FREEDM® One Tight-Buffered, Interlocking Armored Cable, Plenum

24 F, Single-mode (OS2)

CORNING

## Specifications

### General Specifications

Environment	Indoor/Outdoor Cables
Application	Aerial, Direct Buried, Duct, General Purpose Horizontal, (Vertical Riser, Plenum)
Cable Type	Tight-Buffered
Product Type	Interlocking armor
Flame Rating	Plenum (OFCP)
Fiber Category	Single-mode (OS2)

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

### Cable Design

Central Element	Dielectric
Fiber Count	24
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tensile Strength Elements and/or Armoring - Layer 1	Water-swellable strength members
Inner Jacket Material	Flame-Retardant, UV-Resistant
Tensile Strength Elements and/or Armoring - Layer 2	Interlocking armor
Number of Ripcords	2
Outer Jacket Material	Flame-Retardant, UV-Resistant
Outer Jacket Color	Black

### Mechanical Characteristics Cable

Nominal Inner Cable Diameter	8.0 mm (0.31 in)
Nominal Outer Diameter	13.7 mm (0.54 in)
Weight	161.4 kg/km (108.5 lb/1000 ft)
Min. Bend Radius Installation	205.5 mm (8.1 in)
Min. Bend Radius Operation	137 mm (5.4 in)

# FREEDM® One Tight-Buffered, Interlocking Armored Cable, Plenum

24 F, Single-mode (OS2)

CORNING

## Mechanical Characteristics Cable

Max. Tensile Strength, Short-Term	1350 N (300 lbf)
Max. Tensile Strength, Long-Term	400 N (90 lbf)

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Fiber Specifications

### Optical Characteristics (cabled)

Fiber Name	SMF-28e® fiber
Fiber Category	G.652.D
Fiber Code	E
Performance Option Code	31
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / 0.50 dB/km

## Ordering Information

Part Number	024E8P-31131-A3
Product Description	FREEDM® One Tight-Buffered, Interlocking Armored Cable, Plenum, 24 F, Single-mode (OS2)
EAN Code	4056418198576



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

CORNING