


760018051 | P-096-DS-8W-FMUYL

Plenum Distribution Cable, 96 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Total Fiber Count	96
Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Fiber Type, quantity	96
Fibers per Subunit, quantity	12
Jacket Color	Yellow

Dimensions

Buffer Tube/Subunit Diameter	5.77 mm 0.23 in
Cable Weight	361.0 lb/kft 537.0 kg/km
Diameter Over Jacket	22.91 mm 0.90 in
Subunit, quantity	8

Physical Specifications

Minimum Bend Radius, loaded	34.4 cm 13.5 in
Minimum Bend Radius, unloaded	22.9 cm 9.0 in
Tensile Load, long term, maximum	90 lbf 400 N

760018051 | P-096-DS-8W-FMUYL

Tensile Load, short term, maximum 300 lbf | 1335 N
Vertical Rise, maximum 76.0 m | 249.3 ft

Flame Test Specifications

Flame Test Listing NEC OFNP (ETL) and c(ETL)
Flame Test Method NFPA 262

Environmental Specifications

Environmental Space Plenum
Installation Temperature 0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression 10 N/mm | 57 lb/in
Compression Test Method FOTP-41 | IEC 60794-1 E3
Flex 100 cycles
Flex Test Method FOTP-104 | IEC 60794-1 E6
Impact 4.34 ft lb | 5.88 N-m
Impact Test Method FOTP-25 | IEC 60794-1 E4
Strain See long and short term tensile loads
Strain Test Method FOTP-33 | IEC 60794-1 E1
Twist 10 cycles
Twist Test Method FOTP-85 | IEC 60794-1 E7

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method IEC 60794-1 F9
Low High Bend -20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method FOTP-37 | IEC 60794-1 E11
Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Qualification Specifications

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

