

S3230 Series

Stand-alone Gigabit Ethernet Remotely Managed NID 10/100/1000Base-T to 1000Base-X with OAM/IP-Based Management



S3231-1040

Features

- MEF 9, 14 and 21 certified
- 802.3ah Link OAM
- ITU Y.1731
- 802.1ag Service OAM
- 10K Jumbo Frame Support
- Two selectable Remote Management modes:
 - IP-Based Remote Management
 - In-Band (remote device managed by local peer)
- Auto-MDI/MDIX
- Auto-Negotiation
- Pause
- Transparent Link Pass Through
- Far-End-Fault (FEF)
- Remote Loopback
- Field Upgradeable Firmware
- IEEE 802.1p QoS packet classification
- IPv4 IP TOS, DiffServ and IPv6 traffic class QoS classification
- IEEE 802.1q VLAN and double VLAN tagging with 4096 VIDs
- DHCP client
- SNTP
- TFTP
- RADIUS client
- RMON counters for each port
- Bandwidth profiling
- DMI Optical Management
- Cable diagnostic function for copper ports
- SSH
- Telnet
- Command Line Interface (CLI)
- Web management
- Focal Point Management
- SNMP v1, v2c, and v3
- USB port for basic setup
- Management VLAN

The ION 3230 Series of Network Interface Devices (NIDs) are multi-service NIDs that provide SLA-assurance and advanced fault management that is compliant with MEF and IEEE standards. The ION 3230 Series are designed for business Ethernet and mobile backhaul deployments. The ION S3230 Series are MEF 9, 14 and 21 certified. The ION 3230 Series is a 10/100/1000Mbps product with advanced features including – IEEE 802.1ag Service OAM, IEEE 802.3ah Link OAM, ITU Y.1731 Performance Monitoring, VLAN, QoS, SSH/SSL, jumbo frame support and bandwidth allocation.

Applications include: Ethernet in the First Mile (EFM), Fiber to the Premises (FTTP), E-Line Services (EPL & EVPL), and Enterprise Markets.

Specifications

Standards	IEEE 802.3 IEEE 802.3ah IEEE 802.3ag IEEE 802.1P IEEE 802.1Q
Data Rate	Copper: 10/100/1000 Mbps Fiber: 1000 Mbps
Filtering Address	8K MAC Addresses
Max Frame Size	10,240 bytes
Dimensions	Width: 3.25" [82 mm] Depth: 6.5" [165 mm] Height: 1" [25 mm]
Power Input	100-240 VAC, 1A
Power Output	12 VDC, 1.25A
Environment	Operating: 0°C to 50°C Storage: -25°C to 85°C Humidity: 5% to 95% (non-condensing) Altitude: 0 – 10,000 ft.
Weight	2 lbs. [0.90 kg]
Compliance	EN55022 Class A, EN55024, UL60950, CE Mark
Warranty	Lifetime



Ordering Information

S3230-1013
10/100/1000Base-T (RJ-45) [100 m]
to 1000Base-SX 850nm multimode (SC)
[62.5/125 µm fiber: 220 m/722 ft.] [50/125
µm fiber: 550 m/1804 ft.] Link Budget: 8.5 dB

S3230-1014
10/100/1000Base-T (RJ-45) [100 m]
to 1000Base-LX 1310nm single mode (SC)
[10 km/6.2 mi.] Link Budget: 10.5 dB

***S3230-1040**
10/100/1000Base-T (RJ-45) [100 m]
to (1) 100/1000Base-X SFP Slot (empty)

***S3231-1040**
10/100/1000Base-T (RJ-45) [100 m]
to (2) 100/1000Base-X SFP Slots (empty)

Optional Accessories (sold separately)

SFP Modules

Mounting Options

WMBL
Wall Mount Bracket 4" [102 mm]

Note: all units feature USB port for local management application.

*S3230-1040 and S3231-1040 have SGMII support for use with 10/100/1000Base-T copper SFPs.

Power Supply Included

To order the corresponding country specific power supply, add the extension from the list below to the end of the SKU; Ex: S3230-1013-NA

-NA = Country Code

- NA = North America
- LA = Latin America
- EU = Europe
- UK = United Kingdom
- SA = South Africa
- JP = Japan
- OZ = Australia
- BR = Brazil