

# Closet Connector and Splice Housing (CCS)

Holds 2 CCH connector panels, 2 2R/2S or 1 4R/4S splice trays

CORNING

The closet connector splice housing (CCS) combines the benefits of a connector housing and splice housing into a single unit. This cost-effective design approach reduces the number of housings being installed, saving the user valuable and expensive rack space.

The CCS is a rack-mounted product that is to be used in premises applications in the main cross-connect (MC) or intermediate cross-connect (IC) locations. To optimize the flexibility of this design, Corning recommends the use of pigtailed panels to reduce installation time and improve quality. These panels are available in a variety of connector types and come complete with factory-installed and -tested connectorized pigtails.

Product will fit in either 19- or 23-in equipment racks or cabinets. The housing is built to be mounted in a 19-in rack or cabinet. Optional 23-in brackets are also available. A field-installable lock kit is available for both the front and rear doors.



Part Number: CCS-01U

## Features and Benefits

**Durable, polycarbonate-tinted front door for viewing jumpers**

Ideal for pigtail splicing

**Supports single-mode and multimode applications**

Suitable for loose tube, tight-buffered and ribbon cables

**Offers flexibility for mounting in equipment racks or cabinets**

**Multiple cable entry and jumper exit locations**

**Accommodates splice trays for fusion and mechanical splices**

Individual splice tray access

## Specifications

General Specifications	
Application	Enterprise Networks
Mounting Type	Rack 19-in, Rack 23-in
Product Type	Rack-Mountable Hardware

# Closet Connector and Splice Housing (CCS)

Holds 2 CCH connector panels, 2 2R/2S or 1 4R/4S splice trays

CORNING

## Design - Hardware

Housing Color	Black
Housing Type	CCS
Height Unit	1U
Locking Availability	Front or rear
Number of Panels per Housing	2
Panel or Module Type	CCH
Splice Tray Options	Up to (2) category 2R, 2S or 2M (1) category 4R, 4S or 4M

## Mechanical Characteristics

Dimensions (HxWxD)	4.4 cm x 43.25 cm x 30.5 cm (1.75 in x 17 in x 12 in)
--------------------	---

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Ordering Information

Part Number	CCS-01U
Product Description	Closet Connector and Splice Housing (CCS), holds 2 CCH connector panels, 2 2R/2S or 1 4R/4S splice trays
EAN Code	4056418194233

## Shipping Information

Units per Delivery	1/1
Shipping Weight	1.7 kg (4 lb)
Package Contents	Housing (fits 19-in rack); installation guide; 2 blank panels; 2 mounting ears for 23-in rack; 8 #10-32 x 0.5-in mounting screws, for 23-in mounting ears; 4 #10-32 x 0.5-in mounting screws; 4 #12-24 x 0.50-in threaded mounting screws; twelve 1/8 x 4-in tie wrap, white; 2 central member strain-relief clamp kits; eight-position splice holder with adhesive; FBR organizer holder for 2 step-slot organizers, with adhesive; 2 step slot fiber organizers for RTV splices

CORNING