UniCam® Connector, LC, Organizer Pack

Organizer Pack, 62.5 µm multimode (OM1)



Corning UniCam® high-performance connectors offer best-in-class optical performance in a fast, easy field-termination solution. These high-precision zirconia ceramic ferrule connectors assured exceptional insertion loss – 0.1 dB typical/0.5 dB maximum per connector pair for multimode, 0.2 dB typical/0.5 dB maximum per connector pair for single-mode. Installation of an LC, SC or ST® compatible connector can be accomplished in about 50 seconds to one minute with the UniCam high-performance tool kit.

The lightweight, hand-held installation tool and high-performance precision cleaver virtually eliminate human variability during installation, ensuring terminations are right the first time, every time. This kit was designed with consideration for network installers, from the cleaver, with its intuitive, hand-held precision design and dual-clamp precision hold, to the installation tool, with its immediate go/no-go feedback signal indicating proper mating of the field fiber to the fiber stub. Installation is as easy as strip, clean, cleave, cam and crimp, with exceptional optical performance assured. Every UniCam® connector is assured to meet the published specification at the time of installation or Corning will replace it.

Organizer packs include 900 µm boots only.



Part Number: 95-000-99-Z

Features and Benefits

Performance guaranteed

100 percent yield guarantee

Broad operating temperature (-40° to +75°C)

Utility and flexibility

Factory-polished end face

Consistent optical performance

Fast termination and no consumables

Low installation cost

Minimum insertion loss

Optimum optical performance

Standards

Approvals and Listings Passed EIA/TIA 568-B.3

Intermateability Connectors are FOCIS

compliant with TIA/EIA 604-10A and IEC61754-20

UniCam® Connector, LC, Organizer Pack

Organizer Pack, 62.5 µm multimode (OM1)



Specifications

General Specifications	
Technology	No-Epoxy/No-Polish
Keyed	No
Product Type	Field-Installable Connectors
Corning Logo	Yes
Packaging	Organizer Pack
Fiber Category	62.5 μm MM (OM1)

Temperature Range	
Operation	-40 °C to 75 °C exceeding EIA/TIA 568-B.3 (-40 °F to 167 °F exceeding EIA/TIA 568-B.3)

Design - Connector	
Connector Type	LC
Ferrule Material	Ceramic
Housing Material	Composite
Housing Color	Beige
Boot Color	Beige

Mechanical Specifications - Connector	
Durability	≤ 0.2 dB change by 500 rematings, FOTP-21
Temperature Cycling	≤ 0.3 dB IL, -40° to +75°C, 21 cycles
Nominal Fiber Outer Diameter	125 µm
Tensile Strength Jacketed Cable	50 N, change \leq 0.2 dB, FOTP-6 (11 lb, change \leq 0.2 dB, FOTP-6)
Tensile Strength 900 μm Cable	4.9 N, change \leq 0.2 dB, FOTP-6 (1.1 lb, change \leq 0.2 dB, FOTP-6)

Optical Specifications - Connector	
Insertion Loss, Typical	0.1 dB
Insertion Loss, Maximum	0.5 dB
Reflectance	≤ -26 dB



UniCam® Connector, LC, Organizer Pack

Organizer Pack, 62.5 µm multimode (OM1)



Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Ordering Information

Part Number	95-000-99-Z
Product Description	UniCam® High-Performance Connector, LC, 62.5 µm multimode (OM1), ceramic ferrule, logo, organizer pack, beige housing, beige boot
EAN Code	4056418196398

Shipping Information

Units per Delivery	25/1
Package Contents	25 connectors, 25 triggers, 25 boots (900 μm)



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

