

AXIS M3024-LVE Network Camera

Outdoor-ready, day/night HDTV fixed dome with IR illumination

The affordably priced, vandal-resistant AXIS M3024-LVE is a HDTV fixed mini dome offering excellent video during day and night-time, in indoor or outdoor environments. It has day/night functionality and built-in IR illuminators, making it ideal for surveillance even in complete darkness. It supports Axis' Corridor Format for vertically oriented video streams. With its 3-axis camera angle adjustment, it can be mounted on walls, ceilings or pendants. AXIS M3024-LVE has support for AXIS Camera Application Platform enabling the installation of intelligent video applications such as people counting. The outdoor-ready camera has IP66 and NEMA 4X ratings for protection against dust, rain and snow.

- > Compact, vandal-resistant, outdoor-ready design
- > HDTV 720p/1 MP
- > Day/night and built-in IR illumination
- > Input/output ports
- > Power over Ethernet







General

AXIS M3024-LVE Network Camera

Camera	
Image sensor	1/4" progressive scan RGB CMOS
Lens	M12 mount, Fixed iris, IR corrected 2.8 mm, F2.0
	Horizontal field of view: 77°
Day and night	Automatically removable infrared-cut filter
Light sensitivity/	Color: 0.8-100000 lux, F2.0, B/W: 0.16 lux, F2.0, 0 lux with IR
minimum illumination	illumination on
Shutter time	1/8000 s to 1/6 s
Camera angle adjustment	Pan ±175°, Tilt 65°, Rotation ±180°
Video	
Video compression	H.264 (MPEG-4 Part 10/AVC) Main Profile Motion JPEG
Resolutions	1280x800 (1 MP) to 320x240
Frame rate	25/30 fps with power line frequency 50/60 Hz
Video streaming	Multiple, individually configurable streams in H.264 and
	Motion JPEG Controllable frame rate and bandwidth
	VBR/CBR H.264
Pan/Tilt/Zoom	Digital PTZ
Image settings	Compression, color, brightness, sharpness, contrast, white
	balance, exposure control, backlight compensation, Wide Dynamic Range – dynamic contrast, text and image overlay,
	mirroring of images, privacy mask
	Rotation: 0°, 90°, 180°, 270°, including Corridor Format
Network	
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, Use
	access log, Centralized Certificate Management
Supported	IPv4/v6, HTTP, HTTPSa, SSL/TLSa, QoS Layer 3 DiffServ, FTP,
protocols	CIFS/SMB, SMTP, Bonjour, UPnP, SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP,
	ARP, SOCKS, SSH
System integra	
Application	Open API for software integration, including VAPIX®
Programming	and AXIS Camera Application Platform; specifications at
Interface	www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection
	ONVIF® Profile S, specification at www.onvif.org
Analytics	Video motion detection, Active tampering alarm
	Support for AXIS Camera Application Platform enabling installation AXIS Video Motion Detection 3, AXIS Cross Line
	Detection, AXIS Digital Autotracking and third-party applications
	see www.axis.com/acap
Event triggers	Analytics, Edge storage events, External input
Event actions	File upload: FTP, HTTP, network share and email Notification: email, HTTP and TCP
	External output activation
	Video recording to edge storage
Data atur!	Pre- and post-alarm video buffering Event data
Data streaming	
Built-in installation aids	Pixel counter

Casing	IP66- and NEMA 4X-rated, IK10 impact-resistant aluminum casing with transparent, polycarbonate cover and dehumidifying membrane, Encapsulated electronics, Captive screws (resitorx 10) Color: White NCS S 1002-B For repainting instructions of skin cover or casing and impact on warranty, contact your Axis partner.
Memory	256 MB RAM, 128 MB Flash
Power	Power over Ethernet IEEE 802.3af/802.3a Type 1 Class 2 max 6.3 W
IR illumination	High-efficiency, long-life 850 nm IR LEDs. Range of reach up to 10 m (33 ft) depending on scene
Connectors	Male RJ45 10BASE-T/100BASE-TX PoE on a 2 m (6.6 ft) network cable, warranty can be maintained even when cable is cut-for more information, contact your Axis partner Terminal block for 1 alarm input and 1 output
Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Operating conditions	-30 °C to 50 °C (-22 °F to 122 °F) Humidity 10–100% RH (condensing)
Approvals	EMC EN 55022 Class B, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24 Safety IEC/EN/UL 60950-22 IEC 62471 Environment EN 50581, IEC 60529 IP66, NEMA 250 Type 4X, IEC 62262 IK10
Dimensions	Ø 132 x 93 mm (Ø 5 3/16 x 3 11/16 in)
Weight	770 g (1.7 lb)
Included accessories	Installation Guide, Windows decoder 1-user license, Drill hole template, Resitorx L-key, Terminal block connector
Optional accessories	AXIS T91 Mount Accessories, AXIS T94F01D Pendant Kit, AXIS T94F01L Recessed Mount Kit, AXIS T94F01M J-Box/Gang Box Plate, AXIS T94F01P Conduit Back Box, AXIS T94F01S Mount Bracket, AXIS T94F02D Pendant Kit with sunshield, Network Cable Coupler IP66, Network Cable Coupler Indoor, Network Cable Coupler Indoor Slim, Skin covers (White/Black)
Video management software	AXIS Companion, AXIS Camera Station and video management software from Axis' Application Development Partners (not included). For more information, see www.axis.com/products/video/software
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility

